

# EXPERIENCE OMRON'S NEW i4H LINE OF SCARA ROBOTS

The **i4H SCARA robot** provides a heavier payload and performance compared to its predecessor. Customers can complete machine loading, palletizing and mechanical assembly in industries such as food & beverage and automotive. Maximize uptime with a first ever on-board display and health lighting indicator. The i4H is available in multiple configurations that include a maximum 850mm reach, 410mm quill, and a floor, wall, or inverted mount.



OMRON **i4H-650H** OMRON **i4-750H** 



OMRON **i4-850H** 



MAINTENANCE FEATURE AVAILABLE SUMMER 2021.



### FOR DEMANDING TASKS

## Gain more out of production with a higher payload and faster cycle time

With an updated robust design, the i4H can achieve a more meaningful and efficient production for your factory needs.

Higher payloads up to 15kg

High-speed cycle times

Available in 650, 750, 850mm reach lengths

• 210 or 410 quill options

Standard model floor/table mounts, with optional wall mount bracket and inverted version for ceiling mounting.



## UPTIME



### Discover OMRON's unique additions to the **SCARA lineup**

OMRON has added a few first ever features that will help reduce downtime, prevent accidents, and make maintenance an easier process.

- First ever on-board display for troubleshooting, maintenance, and visual inspections
- World's first robot health lighting indicator

### 14 ROBOT STATUS LIGHT CODES

Off

Solid White

Solid Blue

Blinking Blue Blinking Green

Solid Red

Blinking Red

24V Not present

System initializing System booting

Idle, 24V present

Operational, Servo enabled **FPGA Communication loss** 

**ESTOP or ERROR** 

### **INTEGRATION**

Getting started with the i4H has never been easier

Integrate with OMRON NJ through EtherCAT and programmable through IEC, along with the rest of OMRON'S-SYSMAC products.



\*AN ETHERNET OPTION FEATURING WIZARD SUPPORT FOR VISION AND PACKAGING APPLICATIONS WILL BE AVAILABLE SUMMER 2021.

# AUTOMATE YOUR PRODUCTION LINE WITH OMRON'S i4H

## Automate your full production line with OMRON

Easily program the i4H robot alongside the rest of OMRON's devices (vision, motion, IO, safety) from OMRON's single programming software, Sysmac. Additionally, OMRON's Sysmac software is able to simulate

your entire production line which reduces troubleshooting time and allows you to achieve very high levels of synchronization between multiple robots or robots and servos, all connected through EtherCAT.



### **DETAILS**

The i4H SCARA (Selective Compliance Assembly Robot Arm) is a 4-axis robot with 3 rotational axes and one translational/ linear axis, ideal for high-speed repeatable applications **Reach:** The OMRON i4H is available in three different ranges: 650mm, 750mm, and 850mm. **Payload:** All three models have a maximum payload of 15 kg.

**Mount:** The i4H can be mounted to the floor, wall, or inverted.

Quill: 210mm Standard, 410mm Long Quill. Controller/Amplifier: The robot includes amplifiers and a robot controller in the base. Two robot controllers are provided, the iCS-ECAT (EtherCAT slave controller), and the iCS-ENET (Standalone Ethernet/IP controller).

NOTE: STANDALONE ETHERNET OPTION AVAILABLE SUMMER 2021.

\*ADEPT CYCLE, IN MM 25/305/25 (SECONDS, AT 20C AMBIENT) WITH 2.0KG PAYLOAD \*\*FAST CYCLE, IN MM (25/305/25) (SECONDS, AT 20C AMBIENT) WITH 2.0KG PAYLOAD BUT WITH ARC MOTION

Product		i4-650H	i4-750H	i4-850H
Reach		650mm	750mm	850mm
Maximum Payload		15kg		
Quill Length		210 / 410mm	210 / 410mm	210 / 410mm
Repeatability	XY (mm)	±0.015	±0.025	±0.025
	Z (mm)	±0.01	±0.01	±0.01
	Theta (deg)	±0.005	±0.005	±0.005
Cycle Times*	Burst (s)	0.44	0.44	
	Sustained (s)	0.48	0.54	0.54
	Blended Burst (s)**	0.37	0.37	0.37

**i4H SCARA ROBOT** 

#### **OMRON Corporation** Industrial Automation Company

Kyoto, JAPAN

Contact: www.ia.omron.com

#### **Regional Headquarters**

OMRON EUROPE B.V.
Wegalaan 67-69, 2132 JD Hoofddorp
The Netherlands

Tel: (31)2356-81-300/Fax: (31)2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2),
Alexandra Technopark,
Singapore 119967
Tel: (65) 6835-3011/Fax: (65) 6835-2711

#### OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A.

Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON ROBOTICS AND SAFETY TECHNOLOGIES, INC. 4225 Hacienda Dr., Pleasanton, CA 94588 U.S.A. Tel: (1) 925-245-3400/Fax: (1) 925-960-0590

#### OMRON (CHINA) CO., LTD.

OMKON (CHINA) CO., LID.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200

#### **Authorized Distributor:**

© OMRON Corporation 2020 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

