Operation

NPN Output



PNP Output



Structure of Sensor I/O Connector



Classification	Wire color	Connector pin No.	Use
DC	Brown	1	Power supply (+V)
	White	2	
	Blue	3	Power supply (0 V)
	Black	4	Output

Dimensions

Note: All units are in millimeters unless otherwise indicated.

Sensors

Through-beam (Pre-wired Models)



E3Z-R61

E3Z-R81 E3Z-D61 E3Z-D62



Retroreflective Models (Connector Models) E3Z-R66 E3Z-R86

Through-beam (Connector Models)

Diffuse-reflective Models



8.2

-17-

M8 connector

Operation selector

Sensing adjuster

M8 connector



Accessories (Order Separately)



Mounting Brackets E39-L104

E3Z -



Material: SUS304 stainless steel

E39-L43

L. S.





7.5

15

15.1





Material: SUS304 stainless steel

R2

R2

-13

E39-L44





25.4

٩

- 8 -

24 — — 34 16 20

25



<u>E3Z</u> ·



Precautions

Be sure to abide by the following precautions for the safe operation of the Sensor.

Wiring

Power Supply Voltage

Make sure that the power supply to the Sensor is within the rated voltage range and do not apply 100 VAC or more if the Sensor is a DC model, or otherwise the Sensor may explode or burn.

Load Short-circuiting

Do not short-circuit the load, otherwise the Sensor may be damaged.

Correct Use

Settings

Power Reset Time

The Sensor is ready to operate 100 ms after the Sensor is turned ON. If the load and Sensor are connected to independent power supplies respectively, be sure to turn ON the Sensor before turning the load ON.

Connections

M8 Metal Connector

- Be sure to connect or disconnect the metal connector after turning OFF the Sensor.
- Hold the connector cover to connect or disconnect the metal connector.
- Secure the connector cover by hand. Do not use any pliers, otherwise the connector may be damaged.
- The proper tightening torque range is between 0.3 and 0.4 N m. Be sure to tighten the connector securely, otherwise the specified degree of protection may not be maintained or the connector may be disconnected due to vibration.

Wiring Mistakes

Do not make mistakes in wiring, such as mistakes in polarity, otherwise the Sensor may be damaged.

Connection without Load

Do not connect power supply to the Sensor with no load connected, otherwise the internal elements may explode or burn.

Operating Environment

Do not use the Sensor in locations with explosive or flammable gas.

Mounting

Sensor Mounting

Use M3 screws to mount the sensor and tighten each screw to a maximum torque of 0.53 N \cdot m.



E39-L104 Mounting Bracket (sold separately)

Adjustment

Slits for Through-beam Models (E39-S65A/B/C/D/E/F (Sold Separately))



ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. E308-E1-1 In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation

Industrial Automation Company

Industrial Sensors Division Sensing Devices and Components Division H.Q. 28th Fl., Crystal Tower Bldg., 1-2-27, Shiromi, Chuo-ku, Osaka 540-6028 Japan Phone: (81)6-6949-6012 Fax: (81)6-6949-6021

Printed in Japan 0799-5M (0799) (Å