Solid State Relays G3 - VD G3F/G3FD

Refer to Warranty and Application Considerations (page 1), Safety Precautions (page 4), and Technical and Safety Information (page 6).

International Standards for G3F Series, Same Profile as MY Power Relays

- Shape-compatible with mechanical relays.
- Certified by UL, CSA, and VDE (model numbers with a suffix of "-VD").
- Socket type, same size as MY Power Relays.
- Operation indicator provided to confirm input (model numbers with "N" before the suffix).





Model Number Structure

■ Model Number Legend



1. Basic Model Name

G3F: Solid State Relay

2. Rated Load Power Supply Voltage

2: 200 VAC

3. Rated Load Current

02: 2 A 03: 3 A

4. Terminal Type

S: Plug-in terminals

5. Zero Cross Function

Blank: Equipped with zero cross functions
L: Not equipped with zero cross function

6. Operation Indicator

Blank: Not equipped with operation indicator
N: Equipped with operation indicator

7. Certification

VD: Certified by UL, CSA, and VDE



1. Basic Model Name

G3F: Solid State Relay

2. Load Power Supply Type

D: DC

03:

3. Rated Load Power Supply Voltage

X: 50 VDC 1: 100 VDC 4. Rated Load Current

3 A

5. Terminal Type

S: Plug-in terminals

6. Operation Indicator

Blank: Not equipped with operation indicator N: Equipped with operation indicator

7. Certification

VD: Certified by UL, CSA, and VDE

Ordering Information

■ List of Models

| Isolation | Zero cross function | Indicator | Rated output load | Rated input voltage | Model |
|--------------------|---------------------|-----------|-------------------------------------|---------------------|---------------|
| Photocoupler | Yes | Yes | 3 A at 100 to 240 VAC (See note 1.) | 5 to 24 VDC | G3F-203SN-VD |
| | | | 2 A at 100 to 240 VAC (See note 1.) | 100/110 VAC | G3F-202SN-VD |
| | | | | 200/220 VAC | 1 |
| Phototriac coupler | No | 1 | 3 A at 100 to 240 VAC (See note 1.) | 5 VDC | G3F-203SLN-VD |
| | | | | 12 VDC | 1 |
| | | | | 24 VDC | 1 |
| Photocoupler | | | 3 A at 4 to 48 VDC (See note 2.) | 5 to 24 VDC | G3FD-X03SN-VD |
| | | | 2 A at 5 to 110 VDC | 100/110 VAC | G3FD-102SN-VD |
| | | | | 200/220 VAC | 1 |
| | | | | 5 to 24 VDC | 1 |
| Photocoupler | Yes | No | 3 A at 100 to 240 VAC (See note 1.) | 4 to 24 VDC | G3F-203S-VD |
| Phototriac coupler | No | 1 | | 5 VDC | G3F-203SL-VD |
| | | | | 12 VDC | 1 |
| | | | | 24 VDC | 1 |
| Photocoupler | | | 3 A at 4 to 48 VDC (See note 2.) | 4 to 24 VDC | G3FD-X03S-VD |
| | | | 2 A at 5 to 110 VDC | | G3FD-102S-VD |

Note: 1. Product is labelled "250 VAC".

- 2. Product is labelled "50 VDC".
- 3. When ordering, specify the rated input voltage.

■ Accessories (Order Separately)

Connecting Sockets

Refer to page 297 for details.

| Item | PYF08A-E | PY08 | PY08-02 | PY08QN(2) |
|----------------|-----------------------------------|--------------------------------------|---------|--------------------|
| Connecting | Front connecting | Back connecting | | |
| 5 | Track mounted/ screw terminals | Solder terminals PCB terminals Wrapp | | Wrapping terminals |
| Hold-down clip | PYC-A1 | PYC-P | | |

Specifications

■ Ratings (at an Ambient Temperature of 25°C)

Input

| Model | Rated voltage | Operating voltage | Impedance | Voltage level | |
|--------------|---------------|-------------------|------------------------|----------------------|----------------------|
| | | | | Must operate voltage | Must release voltage |
| G3F-203SN-VD | 5 to 24 VDC | 4 to 28 VDC | 15 mA max. (See note.) | 4 VDC max. | 1 VDC min. |
| G3F-202SN-VD | 100/110 VAC | 75 to 125 VAC | 41 kΩ±20% | 75 VAC max. | 20 VAC min. |
| | 200/220 VAC | 150 to 250 VAC | 72 kΩ±20% | 150 VAC max. | 40 VAC min. |

OMRON

| Model | Rated voltage | Operating voltage | Impedance | Voltage level | |
|---------------|---------------|-------------------|--|----------------------|----------------------|
| | | | | Must operate voltage | Must release voltage |
| G3F-203SLN-VD | 5 VDC | 4 to 6 VDC | 390 Ω±20% | 4 VDC max. | 1 VDC min. |
| | 12 VDC | 9.6 to 14.4 VDC | 900 Ω±20% | 9.6 VDC max. | |
| | 24 VDC | 19.2 to 28.8 VDC | 2 kΩ±20% | 19.2 VDC max. | |
| G3FD-X03SN-VD | 5 to 24 VDC | 4 to 28 VDC | 1.5 kΩ ^{+20%} / _{-10%} | 4 VDC max. | |
| G3FD-102SN-VD | 5 to 24 VDC | 4 to 28 VDC | 1.5 kΩ ^{+20%} / _{-10%} | 4 VDC max. | |
| | 100/110 VAC | 75 to 125 VAC | 41 kΩ±20% | 75 VAC max. | 20 VAC min. |
| | 200/220 VAC | 150 to 250 VAC | 72 kΩ±20% | 150 VAC max. | 40 VAC min. |
| G3F-203S-VD | 4 to 24 VDC | 3 to 28 VDC | 15 mA max. (See note.) | 3 VDC max. | 1 VDC min. |
| G3F-203SL-VD | 5 VDC | 4 to 6 VDC | 390 Ω±20% | 4 VDC max. | 1 |
| | 12 VDC | 9.6 to 14.4 VDC | 900 Ω±20% | 9.6 VDC max. | |
| | 24 VDC | 19.2 to 28.8 VDC | 2 kΩ±20% | 19.2 VDC max. | |
| G3FD-X03S-VD | 4 to 24 VDC | 3 to 28 VDC | 1.5 kΩ ^{+20%} / _{-10%} | 3 VDC max. | 1 |
| G3FD-102S-VD | | | | | |

Note: Constant-current input circuit.

Output

| Model | Rated load | Applicable load | | | | |
|--|----------------|--------------------|--------------|-----------------------|--|--|
| | voltage | Load voltage range | Load current | Inrush current | | |
| G3F-203SN-VD G3F-203SLN-VD G3F-203S-VD G3F-203SL-VD | 100 to 240 VAC | 75 to 264 VAC | 0.1 to 3 A | 45 A (60 Hz, 1 cycle) | | |
| G3F-203SN-VD | 100 to 240 VAC | 75 to 264 VAC | 0.1 to 2 A | 45 A (60 Hz, 1 cycle) | | |
| G3FD-X03SN-VD G3FD-X03S-VD | 4 to 48 VDC | 3 to 52.8 VDC | 0.1 to 3 A | 18 A (10 ms) | | |
| G3FD-102SN-VD G3FD-102S-VD | 5 to 110 VDC | 3 to 125 VDC | 0.1 to 2 A | 10 A (10 ms) | | |


■ Characteristics

| ltem | G3F-203SN-VD G3F-202SN-VD G3F-203S-VD | G3F-203SLN-VD G3F-203SL-VD | G3FD-X03SN-VD G3FD-X03S-VD | G3FD-102SN-VD | G3FD-102S-VD |
|------------------------|--|--|-------------------------------|---|-----------------------------|
| Operate time | 1/2 of load power source cycle + 1 ms max. (DC input) 3/2 of load power source cycle + 1 ms max. (AC input) | 1 ms max. | 0.5 ms max. | 0.5 ms max. (DC input) 20 ms max. (AC input) | 0.5 ms max. |
| Release time | 1/2 of load power source cycle + 1 ms max. (DC input) 3/2 of load power source cycle + 1 ms max. (AC input) | 1/2 of load power source cycle + 1 ms max. | 2 ms max. | 2.5 ms max. (DC input) 20 ms max. (AC input) | 2.5 ms max. |
| Output ON voltage drop | 1.6 V (RMS) max. | | 1.5 V max. | | |
| Leakage current | 5 mA max. (at 100 VAC) 10 mA max. (at 200 VAC) | 2.5 mA max. (at 100 VAC) 5 mA max. (at 200 VAC) | 5 mA max. (at 50 VDC) | 0.1 mA max. (at 100 VDC) | 0.1 mA max. (at 100 VDC) |
| Insulation resistance | 100 M Ω min. (at 500 VDC) | | | | |
| Dielectric strength | 2,000 VAC, 50/60 Hz for 1 min 1,500 VAC, 50/60 Hz for 1 min | | | | |
| Vibration resistance | Destruction: 10 to 55 to 10 Hz, 0.75-mm single amplitude | | | | |
| Shock resistance | Destruction: 1,000 m/s ² | | | | |
| Ambient temperature | Operating: -30°C to 80°C (with no icing or condensation) Storage: -30°C to 100°C (with no icing or condensation) | | | | |
| Ambient humidity | Operating: 45% to 85% | | | | |
| Certified standards | G3F: UL508, CSA C22.2 No. 14, EN60947-4-3 G3FD: UL508, CSA C22.2 No. 14, EN60950 | | | | |
| Weight | Approx. 50 g | | | | |


Engineering Data

Load Current vs. Ambient Temperature Characteristics

G3F-203SN-VD/203S-VD/203SLN-VD/ 203SL-VD




G3F-202SN-VD G3FD-102SN-VD/102S-VD




One Cycle Surge Current: Non-repetitive

Non-repetitive (Keep the inrush current to half the rated value if it occurs repetitively.)


G3F-203SN-VD/203S-VD/202SN-VD/ 203SLN-VD/203SL-VD



G3FD-X03SN-VD/X03S-VD



G3FD-102SN-VD/102S-VD




Dimensions


Note: All units are in millimeters unless otherwise indicated.







Terminal Arrangement/ Internal Connections



Note: The plus and minus symbols shown in parentheses are for DC loads.

Safety Precautions

■ Precautions for Correct Use

Please observe the following precautions to prevent failure to operate, malfunction, or undesirable effect on product performance.

Connection

The SSR for DC switching use can connect to a load regardless of the polarity of the positive and negative output terminals.

Close Mounting of Multiple Relays

If multiple Relays are mounted side by side, be aware that the outer wall of each SSR works as a heat sink.

The SSR casing serves to dissipate heat. Install the Relays so that they are adequately ventilated. If poor ventilation is unavoidable, reduce the load current by half.

Protective Terminal

When using for AC inductive loads, connect the load terminals of the SSR to an inrush absorber (varistor).

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. K055-E1-05

In the interest of product improvement, specifications are subject to change without notice.