Automation Controller NX502 EtherNet/IP™Unit NX-EIP201



Integrated control, information, and safety brings a new level of speed to manufacturing sites





Integrated control, information, and safety brings a new level of speed to manufacturing sites

Speed is essential in all processes at manufacturing sites to cope with large demand fluctuations.

The NX502 Automation Controller, new product in the NJ/NX Series,

and NX-EIP201 EtherNet/IP Unit integrate control, information, and safety, helping speed up all processes from commissioning through to operation and maintenance.



0116101101



Speed up production improvement Utilize data to boost yield P4

Reduce equipment cycle time while improving quality ------ P5



Speed up production line modification to accommodate demand changes

Increase equipment availability through integrated safety P6



Speed up problem-solving in machines and production lines

Achieve both rapid commissioning and stable operation ------ P7

Features



NX5 integrates control, information, and safety P8
Sysmac Studio improves productivity throughout P10
machine lifecycle
Ordering InformationP11

Utilize data to boost yield

Problem

To increase yield, it is necessary to analyze data (e.g., temperature, pressure, and flow rate) accurately for finding optimal processing conditions and to feed the analysis results back to machines in real time.

Since accurate analysis requires fast and accurate collection of high-resolution data in chronological order, the amount of data is so large that the data transfer to databases becomes a bottleneck.



NX5

With approximately four times the data transfer capability of the previous model ^{*1}, NX5 can transfer all of the increasing amount of high-resolution production data to a database at high speeds.

NX5 also reflects results of database analysis in processing conditions in real time, contributing to defect prevention and yield improvement.



*1. NJ5 Machine Automation Controller



Reduce equipment cycle time while improving quality

Problem

As processing is becoming more and more precise, high-frequency collection of diverse data is required in order to improve product quality early on while maintaining fast equipment cycle times.

Another challenge is insufficient communication bandwidth when the increasing amount of data is transferred to a PC or other system.

NX5

NX5 can update command values to send to servomotors and stepper motors as fast as every 250 μs , enabling smooth cam motion, and high-precision interpolation and phase adjustment between axes.

In addition, NX5 can collect data from all EtherCAT $^{\otimes}$ I/O synchronously with less than 1 μs jitter.

Up to four EtherNet/IP units, whose maximum allowed communications bandwidth per unit is 40,000 pps, can be mounted to NX5, coping with high-capacity communications. Fast cycle times can be maintained, and product quality can be improved early. Complete data collection required for high-precision processing without deviation





Increase equipment availability through integrated safety

Problem

Amid technological innovation such as EV and digital devices, manufacturers need to cope with rapid demand changes by building flexible equipment.

They design software, hardware, and networks in a modular manner in order to efficiently change or add production lines and processes, especially large production lines.

However, network power supply for all processes must be turned off for change or addition because safety communications are configured within the same network segment. This affects a wide area, thereby prolonging lead time.



NX5

NX5 enables you to modularize network configurations including safety as well as software and hardware. Since a process to change is localized, you can adjust and check only the process without stopping the entire line. In addition, up to 8 separate networks and 254 safety connections allow a large production line to be flexibly built. These benefits significantly reduce lead time for line changes.





Achieve both rapid commissioning and stable operation

Problem

Reduction in time required to set up and reliably operate a new machine is always a challenge. It is time- consuming to solve problems that are hard to be reproduced.

Defects and line stoppages during mass production need to be addressed quickly to improve overall equipment effectiveness (OEE).



Collecting more data reduces control performance, limiting collected data.

NX5

NX5 comes with the Automation Playback function as standard, collecting and playing back control behavior data to allow you to quickly identify problems that are hard to be reproduced.

You can reliably use NX5 during mass production because data collection does not affect the control period.

Causes of problems can be quickly analyzed from huge amounts of playback data. This shortens the time required for finding the causes, contributing to increase in machine availability.



Collecting more data does not affect control performance, allowing control behavior data to be easily collected.



NX5 integrates control, information, and safety



Control

Control for fast-cycle, high-precision processing

- \cdot Controls 32 axes with cycle time of 250 μs
- Used motion control servo axes : 256, 128, 64, 32, 16 axes
- Program capacity : 80 MB
- Memory capacity for variables : 260 MB*1

Information

Various networks for diverse information utilization

SQL functionality

• Reliable, rapid, and easy direct access to databases and utilization of production data

MQTT support

• Direct connection to cloud for easy, fast, and secure data collection

OPC UA functionality

· Secure connection to IT systems such as MES and ERP

Expanded EtherNet/IP

• 10 x 1 Gbps ports for high-speed, high-capacity communications (when connecting four NX-EIP201 units)

Safety

2 different open networks ideal for safety control of production lines and machines

Fail Safe over EtherCAT (FSoE)

- High speed and high reliability with redundancy, suitable for safety control in machine
- 254 connections for large and flexible production line

Common Industrial Protocol Safety (CIP Safety)

- High scalability, suitable for safety control across production line
- · Up to 10 separate networks for network modularization

Sysmac Studio improves productivity throughout machine lifecycle

Development environment integrating control, information, and safety

Sysmac Studio - Integrated Development Environment integrates programming, configuration, information, and safety.

Sysmac Studio includes Function Blocks for motion control and database connection, and collections of software functional components Sysmac Libraries can be downloaded from our website. These allow you to quickly build a control, information, and safety system. Fully conforms with IEC
61131-3 standards
PLCopen®Function
Blocks for Motion Control





New functions help reduce development lead time

Intuitive usability

The guide shows where to insert or change a rung or connecting line, allowing users to create programs using their keyboard only.

100	dist, blanc	Manual (un) (185	of score			9
		Parts	inserti	on gu	ide	
	2					
Mar	C: N.O. Inpu	A J: N.C. Input	O: Output	1: FUN	P: FR	Critics.
	1 VI-	-1/1	1/1			0

Users can easily enter instructions using the search editor, without referring to manuals.



Engineering chain integration

Electrical CAD design data can be loaded and automatically added to configurations and variable names.Only different information from the existing project can be imported.



Ordering Information

NX-series NX502 CPU Unit

	Specifications	Specifications			
Product name	Program capacity	Memory capacity for variables	Maximum number	Used motion	Model
	Trogram capacity	Memory capacity for variables	of used real axes	control servo axes	
NX502 CPU Unit		4 MB (Retain attributes) / 256 MB (No Retain attributes)	256 axes	256 axes	NX502-1700
			128 axes	128 axes	NX502-1600
	80 MB		64 axes	64 axes	NX502-1500
			32 axes	32 axes	NX502-1400
			16 axes	16 axes	NX502-1300

EtherNet/IP Unit

Product name	Specifications	Model		
Product name	Communications	Units per CPU Unit Power consumption		Model
EtherNet/IP Unit	Tag data links, Message Communications	4 max.	8.1 W max.	NX-EIP201

Automation Software Sysmac Studio

The Sysmac Studio is the software that provides an integrated environment for setting, programming, debugging and maintenance of machine automation controllers including the NJ/NX-series CPU Units, NY-series Industrial PC, EtherCAT Slave, and the HMI.

For details, refer to your local OMRON website and Sysmac Studio Catalog (Cat. No. P138).

Collection of software functional components Sysmac Library

Please download the Sysmac Library from the following URL and add it to the Sysmac Studio. http://www.ia.omron.com/sysmac_library/

Typical Models

Typical Models		
Product name	Features	Model
MQTT Communications Library	The MQTT communication library is a collection of software functional objects for exchanging Pub / Sub type messages through the MQTT server (MQTT broker).	SYSMAC-XR020
High-speed Analog Inspection Library	The High-speed Analog Inspection Library records analog input values acquired by the High-speed Analog Input Units in chronological order.	SYSMAC-XR016
Temperature Control Library	The Temperature Control Library is used to perform a high-level temperature control.	SYSMAC-XR007
Safety System Monitor Library	The Safety System Monitor Library is used to monitor the safety system information. You can use this library to manage the information of the running safety system.	SYSMAC-XR015
SLMP Communications Library	The SLMP Communications Library is a collection of functional objects that uses the SLMP communications protocol for the Sequencer made by Mitsubishi Electric to carry out communications control.	SYSMAC-XR017

EtherCAT® and Safety over EtherCAT® are registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany.

●ODVA, CIP Safety[™], EtherNet/IP[™], and DeviceNet[™] are trademarks of ODVA.

•Windows is either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

● OPC UA is a trademark of OPC Foundation.

•Some images are used under license from Shutterstock.com.

•Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

[•]Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011 **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388 Authorized Distributor:

©OMRON Corporation 2023-2024 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_3_2 CSM_5_2 E1 04 _____0104 (0.102)

Cat. No. P158-E1-04 0424 (0423)