Emergency Stop Switch (16-dia.) A165E

Separate Construction with Minimal Depth

- · Direct opening mechanism to open contacts in emergencies, such as when they are welded.
- Conforms to EN 60947-5-5.
- · Includes a safety lock to prevent misuse.
- · Features separate construction that allows the Switch to be separated for easier wiring and one-piece construction that allows easier handling.
- · Models available with 3 contacts built into a single block (A165E-U).


Be sure to read the "Safety Precautions" on page 9.

Model Number Structure

List of Models

Diameter of Operation Unit	Function	Model	Shape		
30-mm models	Push-Lock,	A165E	Separate construction		(30-mm model)
40-mm models	turn-reset	A165E-⊡-03U	One-piece construction		(30-mm model)

Model Number Legend (Completely Assembled).....Shipped as a set that includes the Operation Unit



1. Operation Unit Shape and Functions					
Code	Func	Pushbutton			
S	Non-lighted		00 -11-		
LS	Lighted	Push-lock,	30 dia.		
М	Non-lighted	turn-reset	40 dia.		
LM	Lighted				

2 Light Source

z. Ligin	Light Source					
Code	Туре	Operation voltage	Rated voltage			
None	Non-lighted					
24D	LED	24 VAC/ VDC±5%	24 VAC/ VDC			

Note: Models with separate construction (1NC(1) and 2NC(2)) are for normal loads only. One-piece models (3NC(3)) are for either normal loads or microloads.

] 3. Contacts				
Code	Description			
01	1NC(1)			
02	2NC(2)			
03U	3NC(3) *			

4. Code

None

ΡK

Description

Arrows and text printed in white on Pushbutton.

Arrows and text printed in pink on Pushbutton.

* 3NC(3) models have one-piece construction with the contact unit. Only non-lighted models are available.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

and light source.

Ordering Information

List of Sets

Illumination	Rated voltage	Pushbutton color	Pushbutton size	Terminal	Contact form	Model
					1NC(1)	A165E-LS-24D-01
LED	24 VAC/VDC					A165E-LS-24D-01-PK
LED	24 VAC/VDC				2NC(2)	A165E-LS-24D-02
			30 dia.		2NC(2)	A165E-LS-24D-02-PK
			50 dia.		1NC(1)	A165E-S-01
Non lighted					1NC(1)	A165E-S-01-PK
Non-lighted					2NIC(2)	A165E-S-02
					2NC(2)	A165E-S-02-PK
					1NC(1)	A165E-LM-24D-01
LED				Solder terminal	1NC(1)	A165E-LM-24D-01-PK
LED	24 VAC/VDC			Solder terminal	2NIC(2)	A165E-LM-24D-02
			40 dia.		2NC(2)	A165E-LM-24D-02-PK
			40 dia.		4110(4)	A165E-M-01
Non lighted				1NC(1)	A165E-M-01-PK	
Non-lighted	-lighted					A165E-M-02
			-	2NC(2)	A165E-M-02-PK	
		30 dia.			A165E-S-03U	
Non lighted			su dia.	-	3NC(3)	A165E-S-03U-PK
Non-lighted			40 dia			A165E-M-03U
		40 dia.				A165E-M-03U-PK

List of Sets (in Different Colors)

Illumination	Pushbutton color *	Pushbutton size	Terminal	Contact form	Model
	Yellow	- - - 30 dia.	Solder terminal	1NC(1)	A165E-SY-01
	Gray				
Non lighted	Yellow			2NC(2)	A165E-SY-02
Non-lighted	Gray				A165E-SGR-02
	Yellow			3NC(3)	A165E-SY-03U
Gray	Gray				A165E-SGR-03U

* Models with yellow or gray pushbutton colors cannot be used as emergency switches.

Individual Parts (for Switches with Separate Construction)

Operation Units

Appearance	Illumination	Model
	Non lighted	A165E-S
30 dia.	Non-lighted	A165E-S-PK
	Lighted	A165E-LS
		A165E-LS-PK
40 dia.	Non-lighted	A165E-M
	Lighted	A165E-LM

Lamps

Appearance	LED color		Rated voltage	Model
			5 VDC	A16-5DSR
A BB	Red	Bright	12 VAC/VDC	A16-12DSR
			24 VAC/VDC	A16-24DSR

Switches

Appearance	Illumination	Contact form	Model
	Non-lighted	1NC(1)	A165E-01
		2NC(2)	A165E-02
		1NC(1)	A165E-01L
		2NC(2)	A165E-02L

Switch Units

Appearance	Illumination	Contact form	Model
	Lightod	1NC(1)	A165E-R-24D-01
	Lighted	2NC(2)	A165E-R-24D-02

Accessories (Order Separately)

Item	Appearance	Туре	Model	Precautions
Yellow Plate	\bigcirc	Yellow, 45 dia.	A16Z-5070	Use this as an emergency stop nameplate.
Panel Plug		Round	A16ZT-3003	Used for covering the panel cutouts for future panel expansion. Degree of protection: IP40 Color: Black
Tightening Tool			A16Z-3004	Useful for repetitive mounting. Be careful not to tighten excessively.
Extractor			A16Z-5080	Convenient for extracting the Switch and Lamp.

Specifications

Certified Standard Ratings

UL508, CSA C22.2 No.14, CCC(GB/T14048.5) Models with Separate Construction

Rated voltage	Resistive load
125 VAC	5 A
250 VAC	3 A
30 VDC	3 A

Models with One-piece Construction

Rated voltage	Resistive load
125 VAC	1 A
250 VAC	0.5 A
30 VDC	1 A

TÜV(EN60947-5-1)

Models with Separate Construction

Rated voltage	Resistive load
250 VAC	3 A
30 VDC	3 A

Models with One-piece Construction

Rated voltage	Resistive load
250 VAC	0.5 A
30 VDC	1 A

Certified Standards

Certification body	Standards	File No.	
UL *	UL508, CSA C22.2 No.14	E76675	
TÜV SÜD	EN60947-5-1 (certified direct opening), EN60947-5-5	Consult your OMRON representative for details.	
CQC (CCC)	GB/T14048.5		

* Certification for CSA C22.2 No. 14 has been obtained. Separate construction models have been certified for the Switch Unit.

Switch Ratings Models with Separate Construction

Rated voltage	Resistive load
125 VAC	5 A
250 VAC	3 A
30 VDC	3 A

Note: Minimum applicable load: 5 VDC, 150 mA

Models with One-piece Construction

Rated voltage	Resistive load
125 VAC	1 A
250 VAC	0.5 A
30 VDC	1 A

Note: Minimum applicable load: 5 VDC, 1 mA

LED Ratings

(Only for Models with LEDs)

Rated voltage	Rated current	Operation voltage
24 VAC/VDC	8 mA	24 VAC/VDC±5%

Characteristics

	Туре		Emergency Stop Switch		
Item		Non-lighted A165E-S/A165E-M	Lighted A165E-LS/A165-LM	Non-lighted, One-piece construction A165E-U	
Allowable operating Mechanical		20 operations/minute max			
frequency	Electrical	10 operations/minute max.			
Insulation resistance	•	100 MΩ min. (at 500 VDC)			
	Between terminals of same polarity	1,000 VAC, 50/60 Hz for 1	min		
Dielectric strength	Between terminals of different polarity	2,000 VAC 50/60 Hz for 1	min		
-	Between each terminal and ground	2,000 VAC 50/60 Hz for 1	min		
	Between lamp terminals	1,000 VAC, 50/60 Hz for 1 min *1			
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)		within 1 ms)	
C	Destruction	500 m/s ²			
Shock resistance	Malfunction	300 m/s² max. (malfunction within 1 ms)		150 m/s ² max. (malfunction within 1 ms)	
Durability	Mechanical	100,000 operations min.			
Durability	Electrical	100,000 operations min.			
Degree of protection		IP65 Oil-resistant *2	IP65 *2	IP65 Oil-resistant *2	
Electric shock protect	ction class	Class II			
PTI (tracking charact	eristic)	175			
Degree of contamination 3 (EN60947-5-1)					
Weight		Approx. 16 g (in case of 2NC(2) Switches)			
Ambient operating te	emperature	-10 to 55°C (with no icing or condensation)			
Ambient operating h	umidity	35% to 85%			
Ambient storage tem	perature	ure –25 to 65°C (with no icing or condensation)			


***1.**LED not mounted. (Test them with the LED removed.)

***2.** Degree of protection from the front of the panel.

Operating Characteristics

Item	Туре	Characteristics of models with separate construction	Characteristics of models with one-piece construction
Operating force	OF max.	14.7 N	14.7 N
Releasing torque	RF max.	0.1 N·m	0.1 N·m
Pretravel	PT	3.5±0.5 mm	3±0.5 mm

Structure and Nomenclature




* Models with yellow or gray pushbutton colors cannot be used as emergency switches.


A165E

Dimensions


(Unit: mm)




A165E



Accessories



Terminal Arrangement




Note: The L+ and L- terminals are not available with the non-lighted models.

Installation

Mounting to the Panel (Models with Separate Construction)

After installing the Operation Unit, snap in the Switch from the back of the panel.



Safety Precautions

Be sure to read the precautions for all A165E models in the website at: http://www.ia.omron.com/.

Indication and Meaning for Safe Use

	Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.

If the Operation Unit is separated from the Switch Unit, the equipment will not stop, creating a hazardous condition. Always confirm that safety functions are operating before starting operation.

Precautions for Correct Use

Mounting

- Always make sure that the power is turned OFF before mounting, removing, or wiring the Switch, or performing maintenance.
 Electrical shock or fire may result if the power is not turned OFF.
- The tightening torque is 0.29 to 0.49 N·m.

Wiring

- Be sure to use electrical wires that are a size appropriate for the applied voltage and carry current. Perform soldering according to the conditions given below. If the soldering is not properly performed, abnormal heating may result, possibly resulting in fire.
- 1. Hand soldering: 30 W, within 5 s
- 2. Dip soldering: 240°C, within 3 s

Wait for one minute after soldering before exerting any external force on the solder.


- Use non-corrosive resin fluid as the flux.
- Make sure that the electric cord is wired so that it does not touch the Unit. If the electric cord will touch the Unit, then electric wires with a heat resistance of 100°C min. must be used.
- After wiring the Switch, maintain an appropriate clearance and creepage distance.

Operating Environment

- The IP65 model is designed with a degree of protection so that it will not sustain damage if it is subjected to water from any direction to the front of the panel.
- The Switch is intended for indoor use only. Using the Switch outdoor may cause it to fail.

Using the Microload

- Insert a contact protection circuit, if necessary, to prevent the reduction of life expectancy due to extreme wear on the contacts caused by loads where inrush current occurs when the contact is opened and closed.
- The A165E-□U (one-piece construction) allows both a standard load (125 V at 1 A, 250 V at 0.5 A) and a microload. If a standard load is applied, however, the microload area cannot be used. If the microload area is used with a standard load, the contact surface will become rough, and the opening and closing of the contact for a microload may become unreliable.
- The minimum applicable load is the N-level reference value. This value indicates the malfunction reference level for the reliability level of 60% (λ 60) (conforming to JIS C5003).
- The equation, $\lambda \omega = 0.5 \times 10^{-6}$ /time indicates that the estimated malfunction rate is less than 1/2,000,000 with a reliability level of 60%.



LEDs

The LED current-limiting resistor is built-in, so external resistance is not required.

Rated voltage	Internal limiting resistor
24 VAC/VDC	2.4 kΩ

Operating Torque

- Do not exceed an operating torque of 0.49 N·m in the direction of rotation.
- Do not pull the operating button or apply excessive force to any side of the button.


Otherwise it may be damaged.

A165E

Others

- The oil-resistant IP65 uses NBR rubber and is resistant to general cutting oil and cooling oil. Some special oils cannot be used with the oil-resistant IP65, however, so contact your OMRON representative for details.
- If the panel is to be coated, make sure that the panel meets the specified dimensions after coating.
- Due to the structure of the Switch, severe shock or vibration may cause malfunctions or damage to the Switch. Also, most Switches are made from resin and will be damaged if they come into contact with sharp objects. Particularly scratches on the Operation Unit may create visual and operational obtrusions.

Handle the Switches with care, and do not throw or drop them.



Screwdriver

Hammer

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company