CJ series Position Control Units

High-speed, High-precision positioning with 1, 2, or 4 axes

- · Versatile functions and superb performance enable the construction of compact, high-performance machines.
- With its ultra-compact size of 31×90 mm (W \times H), this highly space-efficient Position Control Unit (PCU) enables up to 4 axes of motor control.




CJ1W-NC113

CJ1W-NC413

Features

- Two types to choose from: open collector output and line driver. Because both open collector output and line driver types feature 1-, 2-, and 4axis models, the most appropriate model can be selected for the application at hand.
- Positioning START occurs within 2 ms (maximum speed) after receiving a command from the Programmable Controller. (Refer to the Operation Manual for conditions.)
- High-speed data transfer is possible using INTELLIGENT I/O WRITE (IOWR) and INTELLIGENT I/O READ (IORD) instructions.
- Fine control from low to high speed (500 kpps max.) is possible in 1-pps units.
- Positioning can be done from memory, by writing an operating pattern into the PCU memory in advance. Three position patterns Terminating, Automatic, and Continuous - can be set with completion codes to respond to a wide range of operations. Positioning of up to 100 patterns (sequential data) per one axis can be possible.
- Positioning (direct operation) can be done by direct PLC ladder commands for position data, speed data, and acceleration data. This simplifies control in situations when the target position and speed cannot be decided until immediately before operation begins, or when the target position and speed change due to other circumstances. The target position and speed can also be changed during operation.
- Interrupt feeding moves the axis a specified amount, then stops it, in accordance with an interrupt input. High-speed (0.1 ms max.) processing of the interrupt input signal ensures high-precision interrupt positioning. This helps to maximize feeder precision.
- Easy-to-Use positioning can be possible with versatile functions such as Teaching, Override, Backlash compensation, Zones, Forced interrupt and Acceleration/Deceleration curve.

System Configuration



Ordering Information

International Standards

- The standards are abbreviated as follows: U: UL, U1: UL(Class I Division 2 Products for Hazardous Locations), C: CSA, UC: cULus, UC1: cULus (Class I Division 2 Products for Hazardous Locations), CU: cUL, N: NK, L: Lloyd, and CE: EC Directives.
- Contact your OMRON representative for further details and applicable conditions for these standards.

Position Control Unit

| Unit type | Name | Specifications | | No. of unit numbers | Current consumption (A) Model | | Standarda | |
|--------------------------|--------------|--|---------------------------|------------------------|-------------------------------------|----------------|----------------------------------|---------|
| | Name | Control method/Control output interface | Number of control axes | allocated | 5 V system | 24 V system | Woder | UC1, CE |
| Position control unit | | 1 axis | 1 | 0.25 | - | CJ1W-NC113 | | |
| | control unit | Open-loop control by pulse train output/ Open-collector output | 2 axes | | 0.25 | - | CJ1W-NC213 | |
| | 100 | | 4 axes * | 2 | 0.36 | - | CJ1W-NC413 CJ1W-NC133 UC1, CI | |
| CJ1 | 3. | | 1 axis | 1 | 0.25 | - | CJ1W-NC133 | |
| Special I/O Units | | Open-loop control by pulse train output/ | 2 axes | | 0.25 | - | CJ1W-NC233 | |
| 1/0 Units | a last | Line-driver output | 4 axes * | 2 | 0.36 | - | CJ1W-NC433 | |
| | Space Unit | The ambient operation temperature range can be CJ-series Space Unit is used. | increased to 0 to | 55°C if the C | J1W-SP00 | 01 | CJ1W-SP001 | UC1, CE |

Note: This unit cannot be used with the Machine Automation $\overline{\text{Controller NJ-series}}$.

* The ambient operating temperature of the CJ1W-NC413/NC433 is 0 to 50°C. Allowable power supply voltage range for external power supply is 22.8 to 25.2 V DC.

Software

| Name | Specifications | Number of licenses | Model | Standards |
|---------------|--|--------------------|----------------|-----------|
| FA Integrated | The CX-One is a comprehensive software package that integrates Support | | | |
| Tool Package | Software for OMRON PLCs and components. | 1 license * | CXONE-AL01D-V4 | |
| CX-One | | DVD | CAUNE-ALUID-V4 | _ |
| Ver. 4. 🗆 | CX-One Ver.4. includes CX-Position Ver.2. | | | |

Note: For details, refer to the CX-One Catalog (Cat. No. R134), visit your local OMRON website.

* Multi licenses (3, 10, 30, or 50 licenses) and DVD media without licenses are also available for the CX-One.

Servo Relay Unit/Cables

| Name | Applica | ble units | Applicable drives * | Number of control axes | Cable length | Model | Standards |
|----------------------------|--|----------------------|-----------------------------------|---------------------------|--------------|---------------|-----------|
| | For CJ1W-NC113/133 (No communication supported) | | - | 1 axis | - | XW2B-20J6-1B | - |
| Servo Relay Unit | For CJ1W-NC213/233/4 (No communication sup | | - | 2 axes | - | XW2B-40J6-2B | |
| | For CJ1W-NC113/133/2 (Communication support | | - | 2 axes | - | XW2B-40J6-4A | |
| | | | OMNUC G/G5 Series, | | 0.5m | XW2Z-050J-A14 | |
| | | For CJ1W-NC113 | SMARTSTEP 2 | 1 axis | 1m | XW2Z-100J-A14 | |
| | | FOLCJTW-NCT13 | SMARTSTEP Junior Series | 1 4815 | 0.5m | XW2Z-050J-A16 | |
| | Open-collector output | | SWARTSTEP JUNIOL Selles | | 1m | XW2Z-100J-A16 | |
| | | For CJ1W-NC213/413 | OMNUC G/G5 Series, SMARTSTEP 2 | - 2 axes | 0.5m | XW2Z-050J-A15 | |
| | | | | | 1m | XW2Z-100J-A15 | |
| Position | | | SMARTSTEP Junior Series | | 0.5m | XW2Z-050J-A17 | |
| Control Unit Cables for | | | | | 1m | XW2Z-100J-A17 | |
| Servo Relay | | For CJ1W-NC313 | OMNUC G/G5 Series, SMARTSTEP 2 | - 1 axis | 0.5m | XW2Z-050J-A18 | |
| Unit | | | | | 1m | XW2Z-100J-A18 | |
| | | FOI CJIW-INCSIS | | | 0.5m | XW2Z-050J-A20 | |
| | Line driver evitevit | | SMARTSTEP Junior Series | | 1m | XW2Z-100J-A20 | |
| | Line-driver output | | OMNUC G/G5 Series, | | 0.5m | XW2Z-050J-A19 | 1 |
| | | For CJ1W-NC233/413 | SMARTSTEP 2 | 2 0200 | 1m | XW2Z-100J-A19 | 1 |
| | | FUI CJ100-INC233/413 | | 2 axes | 0.5m | XW2Z-050J-A21 | 1 |
| | | | SMARTSTEP Junior Series | | 1m | XW2Z-100J-A21 | 1 |

* Including models no longer available to order.

Accessories

The Position Control Unit includes the 40-pin solder-type connectors C500-CE404 (socket: Fujitsu FCN-361J040-AU, cover: Fujitsu FCN-360C040-J2/cover: OTAX N360C040J2).

Applicable Connectors

| Name | | Specifications | Model |
|-------------------------|----|--|------------|
| | | 40 pin, soldered, right angle w/cover (included with the Unit) | C500-CE404 |
| | ×. | 40 pin, crimped right angle w/cover | C500-CE405 |
| External I/O Connectors | | 40 pin, Pressure welded, w/o cover | C500-CE403 |
| | শি | 40 pin, soldered, w/cover | C500-CE401 |
| | | 40 pin, crimped w/cover | C500-CE402 |

Mountable Racks

| | NJ system | | CJ system (CJ1, CJ2) | | CP1H system NSJ syst | | stem *1 |
|--------------------------------|---------------|-------------------|----------------------|--|----------------------|-------------------|------------------------|
| Model | CPU Rack | Expansion Rack | CPU Rack | Expansion Backplane | CP1H PLC | NSJ Controller | Expansion Backplane |
| CJ1W-NC113/133/213/233/413/433 | Not supported | | 10 Units | 10 Units (per Expansion Backplane) | 2 Units *2 | Not Supported | 8 Units |

*1. Product no longer available to order.

*2. CJ Unit Adapter CP1W-EXT01 required.

Specifications

Basic Specifications

| 14 | Model | | | | | |
|--|--|--|---|--|--|--|
| Item | CJ1W-NC113/133 CJ1W-NC213/233 | | CJ1W-NC413/433 | | | |
| | 5 V DC (for the PCU itself) | | | | | |
| Power supply voltage | 24 V DC (external power supply) | | | | | |
| | 5 V DC (external power supply; line | driver output only) | | | | |
| | 4.75 to 5.25 V DC (for the PCU itsel | f) | | | | |
| Allowable power supply voltage range | 21.6 to 26.4 V DC (external power s | 22.8 to 25.2 V DC (external power supply) | | | | |
| | 4.75 to 5.25 V DC (external power supply; line driver output only) | | | | | |
| Internal current consumption | 250 mA max. at 5 V DC | 250 mA max. at 5 V DC | 360 mA max. at 5 V DC | | | |
| Current consumption of external power supply | NC113: 30 mA max. at 24 V DC NC213: 50 mA max. at 24 V DC NC133: 10 mA max. at 24 V DC NC233: 20 mA max. at 24 V DC NC133: 60 mA max. at 5 V DC NC233: 120 mA max. at 5 V DC | | NC413: 100 mA max. at 24 V DC NC433: 30 mA max. at 24 V DC NC433: 230 mA max. at 5 V DC | | | |
| External dimensions | 90 (H) \times 31 (W) \times 65 (D) (all models | | | | | |
| Weight | 100 g max. 100 g max. | | 150 g max. | | | |
| Ambient operating temperature | 0 to 55°C | 0 to 50°C * | | | | |

 Note: Specifications not listed above conform to CJ Series general specifications.

 * Refer to Operation Manual 3-3-5 Mounting Precaution for CJ1W-NC413/NC433 for information on the ambient operating temperature of the CJ1W-NC413/433.


Performance Specifications

| 11 | tem | | Model | | | | |
|---------------------------|--------------------------------------|--|--|--|--|--|--|
| | | CJ1W-NC113/133 | CJ1W-NC213/233 | CJ1W-NC413/433 | | | |
| Applicable PLC models | | CJ-series PLCs *1 | | | | | |
| Unit type | 1 | Special I/O Unit | | | | | |
| I/O requirements | Words | 5 words | 10 words | 20 words | | | |
| Controlled driver | | Pulse-train input-type Servo Drive or stepping motor driver NC113/213/413 models have open collector output. NC133/233/433 models have line driver output. | | | | | |
| Control | Control system | Open-loop control by pulse train of | putput | | | | |
| | Number of control axes | 1 axis | 2 axes | 4 axes | | | |
| Control unit | | Pulse | | | | | |
| Positioning operations | | Two types: memory operation and direct operation | | | | | |
| | Independent | 1 axis | 2 independent axes | 4 independent axes | | | |
| | Linear interpolation | None | 2 axes max. | 4 axes max. | | | |
| | Speed control | 1 axis | 2 independent axes | 4 independent axes | | | |
| | Interrupt feeding | 1 axis | 2 independent axes | 4 independent axes | | | |
| Positions Range | | -1,073,741,823 to 1,073,741,823 | pulses *2 | | | | |
| | Data items | 100/axis | | | | | |
| Speeds Range | | 1 pps to 500 kpps | | | | | |
| 0,0000 | Data items | 100/axis | | | | | |
| Acceleration and | Range | 0 to 250 s, until maximum speed | is reached. | | | | |
| deceleration times | Data items | 9/axis for acceleration and decele | eration each | | | | |
| Functions and settings | Origin search | Origin input signal: selectable (N.O. or N.C. contact) Origin compensation: -1,073,741,823 to 1,073,741,823 pulses Origin search speed: High-speed or proximity-speed can be set. Origin detection method: May be set to stop upon origin input signal after proximity input signal has turned ON, to stop upon origin input signal after proximity input signal has turned OFF, to stop upon origin input signal without using proximity input signal, or to stop upon origin input signal after limit input signal has turned OFF. N.O. = Normally open N.C. = Normally closed | | | | | |
| | Jogging | Jogging can be executed at a specified speed. | | | | | |
| | Dwell times | 19/axis can be set from 0 to 9.99 s (unit: 0.01 s). | | | | | |
| | Acceleration/ deceleration curves | Trapezoidal or S-curve (Can be set separately for each axis.) | | | | | |
| | Zones | Zone Flag turns ON when present | t position is within a specified zone | . Three zones can be set for each ax | | | |
| | Software limits | Can be set within a range of -1,0 | 73,741,823 to 1,073,741,823 pulse | es. | | | |
| | Backlash compensation | 0 to 9,999 pulses. Compensation | speed can also be set. | | | | |
| | Teaching | With a command from the PLC, the | ne present position can be taken a | s the position data. | | | |
| | Deceleration stop | The STOP command causes pos time. | itioning to decelerate to a stop acc | ording to the specified deceleration | | | |
| Functions and settings | Emergency stop | Pulse outputs are stopped by an | external emergency stop comman | d. | | | |
| | Present position preset | The PRESENT POSITION PRES value. | ET command can be used to char | nge the present position to a specifie | | | |
| | Override | | nand is executed during positionin Possible to set to a value from 1 to | | | | |
| | Data saving | Saving to flash memory. (Can be written 100,000 times.) Reading from PLC area by data reading instruction. Reading by Support Software and saving to personal computer hard disk or floppy disk. | | | | | |
| | Inputs | Prepare the following inputs for each axis: CW and CCW limit input signals, origin proximity input signal, origin input signal, emergency stop inpu signal, positioning completed signal, interrupt input signal | | | | | |
| External I/O | Outputs | Prepare the following outputs for each axis: Pulse outputs CW/CCW pulses, pulse outputs and direction outputs can be switched. Either error counter reset or origin-adjustment command outputs can be selected depending on the mo | | | | | |
| Pulse output distribution | period | 1-axis operation: 4 ms Linear interpolation: 8 ms | | | | | |
| Response time | | Refer to Operation manual Appendix A Performance Characteristics. | | | | | |
| Self-diagnostic function | | Flash memory check, memory loss check, CPU bus check | | | | | |
| | | | | | | | |

*1. The additional functions supported by unit version 2.0 can be used only when the PCU is installed with a CJ1-H or CJ1M CPU Unit (either CPU Unit Ver. 2.0 or Pre-Ver. 2.0 CPU Unit). These functions cannot be used if the PCU is installed with a CJ1 CPU Unit. For details on Unit versions, refer to Unit Versions of CJ-series Position Control Units on Operation manual page vi. (Final order entry date for CJ1M:The end of March, 2021)

*2. When performing linear interpolation, the distances that can be moved will vary.

External Interface



LED Indicators

| Name | Color | Status | Explanation |
|------|-----------|----------|--|
| | 0 | Lit | Lit during normal operation. |
| RUN | RUN Green | | Hardware error, or PLC notified of PCU error. |
| 500 | Red | Lit | An error has occurred. |
| ERC | Red | Not lit | No error has occurred. |
| ERH | Red | Lit | An error has occurred IN the CPU Unit. |
| ЕКП | Red | Not lit | No error has occurred at the CPU Unit. |
| | | Lit | Pulses are being output to the X axis (either forward or reverse). |
| Х | Orange | Flashing | An error has occurred, such as incorrect cable type for the X axis or faulty data. |
| | | Not lit | None of the above has occurred. |
| | | Lit | Pulses are being output to the Y axis (either forward or reverse). |
| Y | Orange | Flashing | An error has occurred, such as incorrect cable type for the Y axis or faulty data. |
| | | Not lit | None of the above has occurred. |
| | | Lit | Pulses are being output to the Z axis (either forward or reverse). |
| Z | Orange | Flashing | An error has occurred, such as incorrect cable type for the Z axis or faulty data. |
| | | Not lit | None of the above has occurred. |
| | | Lit | Pulses are being output to the U axis (either forward or reverse). |
| U | Orange | Flashing | An error has occurred, such as incorrect cable type for the U axis or faulty data. |
| | | Not lit | None of the above has occurred. |

Note: 1. For the CJ1W-NC113/NC133, this applies only to the X axis; for the CJ1W-NC213/NC233, it applies only to the X and Y axes. 2. When not all of the axes are used for the CJ1W-NC213/NC233/ NC413/NC433, either connect the CW/CCW limit inputs for the unused axes to the input power supply and turn them ON or set the contact logic to N.O. Connect the emergency stop to the input common and turn it ON. If it is not connected, the ERC indicator will light. Operation will be normal, however, for all axes that are used.

CJ1W-NC

Functions Supported by Each Unit Version of Position Control Unit

| | Unit Version | Pre-Ver. 2.0 | Ver. 2.0 | Ver. 2.3 | | |
|------------------|---|--------------------------------|--|--|--|--|
| Internal sys | tem software version | 1.0 | 2.0 | 2.3 | | |
| CJ-series Po | osition Control Units | CJ1W-NC113/133/213/233/413/433 | | | | |
| | Changing the acceleration for a multiple start during relative movement or absolute movement in direct operation | Not supported | Supported | Supported | | |
| Functions | Changing acceleration/deceleration time during jog operation | Not supported | Supported | Supported | | |
| | Setting acceleration/deceleration time for axis parameters until the target speed is reached | Not supported | Supported | Supported | | |
| | Easy backup function | Not supported | Supported | Supported | | |
| | Setting number of unused axes | Not supported | Not supported | Supported | | |
| | Setting CW/CCW pulse output direction | Not supported | Not supported | Supported | | |
| | Setting origin search pattern | Not supported | Not supported | Supported | | |
| | Position data setting when origin signal stops | Not supported | Not supported | Supported | | |
| | Setting jog operation | Not supported | Not supported | Supported | | |
| | Setting deviation counter reset output signal | Not supported | Not supported | Supported | | |
| | Checking parameters and data at startup | Not supported | Not supported | Supported | | |
| Support Software | | CX-Position Ver. 1.0 or later | CX-Position Ver. 1.0 *1 CX-Position Ver. 2.0 or later | CX-Position Ver. 1.0 *1 CX-Position Ver. 2.0 *2 CX-Position Ver. 2.1 *2 CX-Position Ver. 2.2 or later | | |


Note: The Position Control Unit must be installed with CJ1-H or CJ1M CPU Unit to use the above functions supported for Position Control Unit Ver. 2.0. These functions cannot be used if the Position Control Unit is installed with a CJ1 CPU Unit. (Final order entry date for CJ1M:The end of March, 2021)
 *1. With CX-Position Ver. 1.0, new functions added to Position Control Units Ver. 2.0 or higher cannot be used.
 *2. With CX-Position Ver. 2.0 and CX-Positon Ver. 2.1, new functions added to Position Control Units Ver. 2.3 or higher cannot be used.

CJ1W-NC

Connecting Connectors Using Servo Relay Units

Wiring requires the dedicated cables.

Position Control Unit Cables, Servo Relay Unit, Servo Drive Cable are sold separately.



UP : OMNUC U Series (750 W max.)


* Two Servo Drive Cables are required if 2-axis control is performed using one Position Control Unit.

(Unit: mm)

Dimensions


CJ1W-NC113/213/413 NC133/233/433






Note: The above diagram is for the CJ1W-NC413.

Mounted Dimensions



CJ1W-SP001



Related Manuals

| Manual number | | Model | Name | Contents |
|---------------|----------|--------------------------------|--|---|
| English | Japanese | Model | Name | Contents |
| W397 | SBCE-315 | CJ1W-NC113/133/213/233/413/433 | Position Control Units Operation Manual | Provides information on operating and installing Position Control Units, including details. on basic settings, memory operation, direct operation from CPU and other functions. |
| W433 | SBCE-324 | CXONE-AL D-V | CX-Position Operation Manual | Provides an overview of CX-Position, its functions, and the system configuration, installation, and troubleshooting. |

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company