

Oil-resistant Limit Switches D4ER-□N

Preliminary Version

Even Better Oil Resistance Than D4E-N Switches

- HNBR/fluororubber used for superior resistance to oil.
 Prevents infiltration of oil from moving sections.
- Fluorine resin cable that withstands cutting oils is provided as a standard feature.
- Models available with SmartClick connectors for each connection.
- Minute load model with gold cladding is optimal for electronic control.
- Approved by EN (TÜV).
- Same mounting pitch as D4E-N Switches.
- IP67G degree of protection (JIS C0920 Annex 1) *



Be sure to read *Safety Precautions* on page 11 to 12 and *Safety Precautions for All Limit Switches*.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

* The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards). The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.


Features

HNBR/Fluororubber for Superior Resistance to Oil



Moving sections are protected from infiltration of oil.

Important Sealing Sections



Standard-feature Fluorine Resin Cable That Withstands Cutting Oils

In addition to prewired models, models are also available with prewired SmartClick connectors for easy connection.



Applications

Table Overrun Detection



Table Position Detection



Model Number Structure

Model Number Legend (Not all combinations are possible. Ask your OMRON representative for details.)

D4ER-(1)(2)(3)

(1) Rated Current

1: 1 A at 30 VDC 2: 0.1 A at 30 VDC (2) Actuator

A: Roller plunger B: Crossroller plunger

C: Plunger

D: Sealed roller plunger

E: Sealed crossroller plunger

G: Roller lever

L: Long roller plunger

(4) Pre-wired Connector

-DTK1EJ: Pre-wired connector

(30-cm oil-resistant cable, M12 Smartclick connector)

None: No connector (oil-resistance cable: 2 m)

Note: D4ER-□N Switches are not available with operation indicators.

(3) Terminals

21: Cable (right-hand)

22: Cable (left-hand)

Note: The terminal specifications in model numbers are not the same for D4ER- N and D4E Switches.

Comparison of New and Old Terminal Models

Model Location of lead outlet	D4ER-□N	D4E
Right-hand	D4ER-□□21N	D4E-□□21
Left-hand	D4ER-□□22N	D4E-□□23
Bottom	-	D4E-□□22

Ordering Information

	Type	Cable	e type
			purpose
		Right-hand	Left-hand
Actuator		Model	Model
Roller plunger	þÞ	D4ER-1A21N	D4ER-1A22N
Crossroller plunger	帥	D4ER-1B21N	D4ER-1B22N
Plunger	帥	D4ER-1C21N	D4ER-1C22N
Sealed roller plunger	þ	D4ER-1D21N	D4ER-1D22N
Sealed crossroller plunger	4	D4ER-1E21N	D4ER-1E22N
Roller lever	<u></u>	D4ER-1G21N	D4ER-1G22N
Long roller plunger		D4ER-1L21N	D4ER-1L22N

	Туре	Cable type				
		Micro	oload			
		Right-hand	Left-hand			
Actuator		Model	Model			
Roller plunger	胂	D4ER-2A21N	D4ER-2A22N			
Crossroller plunger	臣	D4ER-2B21N	D4ER-2B22N			
Plunger	鱼	D4ER-2C21N	D4ER-2C22N			
Sealed roller plunger		D4ER-2D21N	D4ER-2D22N			
Sealed crossroller plunger	4	D4ER-2E21N	D4ER-2E22N			
Roller lever		D4ER-2G21N	D4ER-2G22N			
Long roller plunger		D4ER-2L21N	D4ER-2L22N			

	Туре	Pre-wired Co	onnector type
		General-	-purpose
		Right-hand	Left-hand
Actuator		Model	Model
Roller plunger	ÞÞ	D4ER-1A21N-DTK1EJ	D4ER-1A22N-DTK1EJ
Crossroller plunger	盘	D4ER-1B21N-DTK1EJ	D4ER-1B22N-DTK1EJ
Plunger	鱼	D4ER-1C21N-DTK1EJ	D4ER-1C22N-DTK1EJ
Sealed roller plunger	<u>A</u>	D4ER-1D21N-DTK1EJ	D4ER-1D22N-DTK1EJ
Sealed crossroller plunger	4	D4ER-1E21N-DTK1EJ	D4ER-1E22N-DTK1EJ
Roller lever	<u> </u>	D4ER-1G21N-DTK1EJ	D4ER-1G22N-DTK1EJ
Long roller plunger		D4ER-1L21N-DTK1EJ	D4ER-1L22N-DTK1EJ

	Туре	Pre-wired Connector type			
		Micro	load		
		Right-hand	Left-hand		
Actuator		Model	Model		
Roller plunger	ф Д	D4ER-2A21N-DTK1EJ	D4ER-2A22N-DTK1EJ		
Crossroller plunger	盘	D4ER-2B21N-DTK1EJ	D4ER-2B22N-DTK1EJ		
Plunger	盘	D4ER-2C21N-DTK1EJ	D4ER-2C22N-DTK1EJ		
Sealed roller plunger	Þ	D4ER-2D21N-DTK1EJ	D4ER-2D22N-DTK1EJ		
Sealed crossroller plunger		D4ER-2E21N-DTK1EJ	D4ER-2E22N-DTK1EJ		
Roller lever	<u>Ro</u>	D4ER-2G21N-DTK1EJ	D4ER-2G22N-DTK1EJ		
Long roller plunger		D4ER-2L21N-DTK1EJ	D4ER-2L22N-DTK1EJ		

Plug

For models with connectors, select one of the specified Connector Plugs from the following table.

Applicable Limit Switches	Current type	Appearance	No. of conductors	Cable length	Plug
D4ER-□□21N-DTK1EJ	DC	Straight, Smartclick connector	4	2 m	XS5FR-D423-D80-RB1
D4ER-□□22N-DTK1EJ	ВО		4	5 m	XS5FR-D423-G80-RB1

Specifications

Approved Standards

Agency	Standard	File No.	Approved models
TÜV Rheinland	EN60947-5-1	R9551015, J9951016	Ask your OMRON representative for information on approved models.

Ratings

	Standard load								Micro load	
Rated	Non-inductive load (A)				Inductive load (A)			Non-inductive load (A)		
voltage	Resistive load		Resistive load Lamp load		Inductive load Motor load		r load	Resistive load		
	NC	NO	NC	NO	NC	NO	NC	NO	NC	NO
8 VDC	1 –			1		_	0	.1		
14 VDC	1		_		1		_		0.1	
30 VDC	1	1		_		1	-	_	0	.1

Minimum	Standard load	Micro load		
applicable load	160 mA at 5 VDC	1 mA at 5 VDC		

		10 A max.
current	NO	10 A max.

Note: 1. The above current ratings are for a standard current.

- 2. Inductive loads have a power factor of 0.4 min. (AC) and a time constant of 7 ms max. (DC).
- 3. Lamp load has an inrush current of 10 times the steady-state current.
- 4. Motor load has an inrush current of 6 times the steady-state current.

Approved Standard Ratings

TÜV (EN60947-5-1)

 $\begin{array}{ccc} \text{D4ER-}\frac{1}{I} & \frac{G}{II} & \frac{21}{III} & N \end{array}$

Model			Applicable category	Thermal current
I	II	III	and ratings	(Ithe)
1		21/22	DC-12 1 A/30 VDC	1A
2		21/22	DC-12 0.1 A/30 VDC	0.1A

Note:1. □:Actuator variation of item II

2. DC-12 1 A/30 VDC means as follows: Applicable category: DC-12 Rated operating current (Ie): 1 A Rated operating voltage (Ue): 30 VDC


Characteristics

Degree of pro	tection	IP67 (IEC 60529) and IP67G (JIS C0920 Annex 1) *		
	Mechanical	4,000,000 operations min.		
Durability	Electrical	500,000 operations min. (1 A at 30VDC, resistive load) 4,000,000 operations min. (10 mA at 24 VDC, resistive load)		
Operating sp	eed	0.1 mm/sec to 0.5 m/sec		
Operating fre	quency	Mechanical: 120 operations/min Electrical: 30 operations/min		
Rated frequer	псу	50/60 Hz		
Insulation res	sistance	100 MΩ min. (at 500 VDC)		
Contact resistance		15 m Ω max. (initial value for the built-in switch when tested alone)		
Dielectric	Between terminals of same polarity	1,000 VAC, 50/60 Hz for 1 min		
strength	Between each terminal and non- current-carrying metal part	1,500 VAC, 50/60 Hz for 1 min/Uimp at 2.5 kV (EN60947-5-1)		
Rated insulat	ion voltage (Ui)	250V		
Pollution deg	ree (operating environment)	3 (EN60947-5-1)		
Short-circuit	protective device (SCPD)	10 A fuse (type gG or gl, IEC60269 approved)		
Conditional s	hort-circuit current	100 A (EN60947-5-1)		
Conventional	enclosed thermal current (Ithe)	5 A (EN60947-5-1)		
Protection ag	ainst electric shock	Class II (grounding not required with double insulation)		
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude		
Shock	Destruction	1,000 m/s ² max. (IEC68-2-27)		
resistance	Malfunction	300 m/s ² max. (IEC68-2-27)		
Ambient operating temperature		+5°C to +80°C (with no icing)		
Ambient oper	ating humidity	35% to 95%RH (with no condensation)		
Weight		(in case of roller plunger) Cable type (2m): Approx. 140 g Pre-wired Connector type: Approx. 103 g		


Note:1. The following values are initial values.

- 2. The following ratings may vary depending on the model. Contact your OMRON representative for further details.
- * The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards). The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

Structure and Nomenclature



Contact Form Cable type



Pre-wired Connector type




* The position of the positioning piece is not always the same. If using an L-shaped connector causes problems in application, use a straight connector.


Dimensions and Operating Characteristics

(Unit: mm)

Cable type








Operating force	OF	max.	11.77 N
Release force	RF	min.	4.90 N
Pretravel	PT	max.	1.5 mm
Overtravel	ОТ	min.	3 mm
Movement Differential	MD		(0.1 mm)
Operating Position	OP		31.4±0.8 mm

():Reference Value

Cross Roller Plunger D4ER-1B21N * D4ER-2B21N *






F	OF RF PT OT	max. min. max. min.	11.77 N 4.90 N 1.5 mm 3 mm (0.1 mm)
()P		31.4±0.8 mm
_			

():Reference Value

Plunger D4ER-1C21N * D4ER-2C21N *






OF RF PT OT MD	max. min. max. min.	11.77N 4.90N 1.5 mm 3 mm (0.1 mm)
OP		25.4±0.8 mm

():Reference Value

Sealed Roller Plunger D4ER-1D21N *








(0.1.1)	OF	max.	11.77 N
	RF	min.	4.90 N
	PT	max.	1.5 mm
	OT	min.	3 mm
	MD		(0.1 mm) 41.3±0.8 mm

():Reference Value

Note: Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

Only the model with a terminal specification of 21 is shown. The cable is attached to the left side for models with a terminal specification of 22.








Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

* Only the model with a terminal specification of 21 is shown. The cable is attached to the left side for models with a terminal specification of 22.

Pre-wired Connector type









Note: 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.


- Only the model with a terminal specification of 21 is shown.
 - The cable is attached to the left side for models with a terminal specification of 22.
- 3. The location of the positioning piece on the connector is not always the same.






Note: 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

- **2.** Only the model with a terminal specification of 21 is shown.
- The cable is attached to the left side for models with a terminal specification of 22.
- 3. The location of the positioning piece on the connector is not always the same.





Note: 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

- 2. Only the model with a terminal specification of 21 is shown. The cable is attached to the left side for models with a terminal specification of 22.
- 3. The location of the positioning piece on the connector is not always the same.