Tailor to your needs


Xpectia FJ Vision System


- Customisable Xpectia Vision System
- Fast drag and drop programming
- Choice of ready-made GUIs
- Highly robust, advanced measurement algorithm
- Proven component compatibility



System configuration

Standard Configuration





For Customization

Development environment Application producer





Sample codes and Development Wizard for easy customization are available.

Ordering Information

Controller

CPU	Туре	Dual-task	HALCON installed (See note)	No. of Cameras	Output	Model
Core i5 2.4 GHz		Yes	No	2	NPN	FJ-3000
		Yes	No	4	NPN	FJ-3000-10
		Yes	No	2	PNP	FJ-3005
	Controller integrated	Yes	No	4	PNP	FJ-3005-10
	with LCD	Yes	Yes	2	NPN	FJ-H3000
		Yes	Yes	4	NPN	FJ-H3000-10
		Yes	Yes	2	PNP	FJ-H3005
		Yes	Yes	4	PNP	FJ-H3005-10
		Yes	No	2	NPN	FJ-3050
		Yes	No	4	NPN	FJ-3050-10
Controller integrated Box-type Controller with LCD		Yes	No	2	PNP	FJ-3055
	Boy type Controller	Yes	No	4	PNP	FJ-3055-10
	Box-type Controller	Yes	Yes	2	NPN	FJ-H3050
		Yes	Yes	4	NPN	FJ-H3050-10
		Yes	Yes	2	PNP	FJ-H3055
		Yes	Yes	4	PNP	FJ-H3055-10
Atom 1.6 GHz		No	No	2	NPN	FJ-350
	Boy type Centreller	No	No	4	NPN	FJ-350-10
977	Box-type Controller	No	No	2	PNP	FJ-355
111		No	No	4	PNP	FJ-355-10

Note: HALCON runtime license has been installed. The development of HALCON requires HDevelop.

Development Environment

Туре	Model	Operating environment
Application Producer	FJ-AP1	CPU: Intel Pentium Processor (SSE2 or higher) OS: Windows XP Professional (32bit) Service pack 3 or later, or Windows 7 Professional (32bit) or Enterprise (32bit) or Ultimate (32bit) NET Framework: NET Framework 3.5 or higher Memory: At least 2 GB RAM Available disk space: At least 2 GB Browser: Microsoft® Internet Explorer 6.0 or later Display: XGA (1024×768), True Color (32-bit) or higher Optical drive: CD/DVD drive The following software is required to customize the software: Microsoft® Visual Studio® 2010 Professional

Cameras

Appearance	Туре		Model	Remarks		
	D: 11.10	300,000-pixels	Color	FZ-SC		
100	Digital Cameras	Monochrome		FZ-S		
	Digital Cameras	O million nivele	Color	FZ-SC2M	Lens required	
	Digital Cameras	2 million pixels	Monochrome	FZ-S2M	Lens required	
1 1 1 W	Digital Cameras	5 million pixels	Color	FZ-SC5M2		
	Digital Cameras	5 million pixels	Monochrome	FZ-S5M2		
	0 110: 110	000 000 1 1 1 1 1 1	Color	FZ-SFC		
	Small Digital Cameras	300,000-pixel flat type	Monochrome	FZ-SF	Lens for small cameras	
Harm			Color	FZ-SPC	required	
	Small Digital Cameras	300,000-pixel pen type	Monochrome	FZ-SP		
			Color	FZ-SHC	Lens required	
	High-speed Cameras	300,000-pixels	Monochrome	FZ-SH		
		Wide View (Long-distance)	Color	FZ-SQ100F		
	Intelligent Compact Cameras	Wide View (Short-distance)	Color	FZ-SQ100N	Camera + Lens +	
	Intelligent Compact Cameras	Standard	Color	FZ-SQ050F	High-power Lighting	
		Narrow View	Color	FZ-SQ010F		
	Intelligent Cameras	Wide field of vision	Color	FZ-SLC100	Camera + Zoom, Autofocus	
	intelligent Cameras	Narrow field of vision	Color	FZ-SLC15	Lens + Intelligent Lighting	
	A. dafa O	Wide field of vision	Color	FZ-SZC100	Camera + Zoom, Autofocus	
	Autofocus Cameras	Narrow field of vision Color		FZ-SZC15	Lens	

Cameras Peripheral Devices

Appearance	Туре		Model	Remarks		
	CCTV Lenses		3Z4S-LE Series			
Chis.	Extension Tubes		3243-LE Series	_		
	Low-distortion Lenses		FZ-LEH5/LEH8/LEH12/LEH16/ LEH25/LEH35/LEH50/LEH75/ LEH100	Low distortion lens for 2-million and 5-million Pixel Cameras		
	Lenses for Small Camera		FZ-LES3/LES6/LES16/LES30	Lens for 300,000-pixel Small Cameras		
	Extension Tubes for Small Camera		FZ-LESR	Extension Tubes for 300,000-pixel Small Cameras		
	Intelligent Comore Diffusion Dista	Wide field of vision	FZ-SLC100-DL			
	Intelligent Camera Diffusion Plate	Narrow field of vision	FZ-SLC15-DL	_		
			FZ-SXCRB7018BR-4S	Integrated unit combining special Halation cut illumination, strobe controller and camera (without lens)		
	Halation cut illumination		FZ-LTCRB7018BR-4S	Integrated unit combining special Halation cut illumination and strobe controller		
- 100		1	FZ-LTRB7018BR-4S	Special Halation cut illumination only		
•	For Intelligent Compact Comers	Mounting brackets	FQ-XL/XL2	_		
	For Intelligent Compact Camera	Polarizing Filter Attachment	FQ-XF1	_		

Cables

Appearance	Туре	Cable length:	Model	Remarks
/9	Camera Cable	2 m, 5 m, 10 m (See note 2)	FZ-VS	
/9	Bend resistant Camera Cables	2 m, 5 m, 10 m (See note 3)	FZ-VSB	
.	Right-angle Camera Cable (See note 1)	2 m, 5 m, 10 m (See note 2)	FZ-VSL	
/9	Long-distance Camera Cable	15 m (See note 4)	FZ-VS2	_
	Long-distance Right-angle Camera Cable	15 m (See note 4)	FZ-VSL2	_
	Cable Extension Unit	Maximum cable length: 45 m (Up to two Extension Units and three Cables can be connected.) (See note 5)	FZ-VSJ	
.9	Monitor Cable	2 m, 5 m	FZ-VM	
	Parallal Cabla	2 m, 5 m	FZ-VP	
	Parallel Cable	2 m, 5 m, Connector-type	FZ-VPX (See note 6)	

Note: 1. This Cable has an L-shaped connector on the Camera end.

- The 10-m Cable cannot be used for the Intelligent Camera, Autofocus Camera and 5-million pixel camera.
 The 10-m Cable cannot be used for the Intelligent Camera, Autofocus Camera, 2-million pixel camera and 5-million pixel camera.
- 4. The 15-m Cable cannot be used for the Intelligent Camera, Autofocus Camera and 5-million pixel camera.
- 5. Maximum cable length depends on type of camera and cable length to connect. For details, refer to "Cameras / Cables Connection Table" on page 7.
- 6. Connector-Terminal Block Conversion Units can be connected (Recommended Products: OMRON XW2B-50G4/50G5, XE2D-50G6).

Peripheral Devices

Appearance		Туре		Model	Remarks
	LCD Monitor			FZ-M08	For box-type controller
4	USB Memory			FZ-MEM1G	Capacity: 1 GB
	VESA attachment			FZ-VESA	For installing the controller integrated with LCD
	Desktop controller sta	and		FZ-DS	For installing the controller integrated with LCD
	Lighting Controller	For FL-Series		FL-TCC1	
7	Strobe Controller	For 3Z4S-LT Series	One channel	Manufactured by MORITEX Corporation 3Z4S-LT MLEK-C100E1TS2	Required to control external lighting from a Controller
			One channel	FZ-LTA100	
of the second	Strobe Controller	troller For FZ-LT Series Two o		FZ-LTA200	
_	Adapter for the strobe	controller	1	Manufactured by MORITEX Corporation 3Z4S-LT LBK-003	Required to mount a strobe controller on a 5-million pixel camera when using 3Z4S-LT series
				3Z4S-LT Series	
_	External Lighting			FZ-LT Series	_
				FL-Series	

Lenses

High-resolution, Low-distortion Lenses

	, =								
Model	FZ-LEH5	FZ-LEH8	FZ-LEH12	FZ-LEH16	FZ-LEH25	FZ-LEH35	FZ-LEH50	FZ-LEH75	FZ-LEH100
Appearance	42 dia. 38.7	34 dia. 41.6	34 dia. 37.0	33 dia. 36.5	33 dia. 39.5	34 dia. 36.5	34 dia. 55.0	36 dia. 51.0	42 dia. 70.0
Focal length	5mm	8mm	12.5mm	16mm	25mm	35mm	50mm	75mm	100mm
Brightness	F2.8	F1.4	F1.4	F1.4	F1.4	F2	F2.8	F2.5	F2.8
Filter size	M40.5 P0.5	M27.0 P0.5	M27.0 P0.5	M27.0 P0.5	M27.0 P0.5	M27.0 P0.5	M27.0 P0.5	M34.0 P0.5	M40.5 P0.5

The 5-mm Extension Tubes (3Z4S-LE ML-EXR) cannot be used with FZ-LEH25 Lenses.

CCTV Lenses

Model	3Z4S-LE ML-0614	3Z4S-LE ML-0813	3Z4S-LE ML-1214	3Z4S-LE ML-1614	3Z4S-LE ML-2514	3Z4S-LE ML-3519	3Z4S-LE ML-5018	3Z4S-LE ML-7527	3Z4S-LE ML-10035
Appearance	30 dia. 30	30 dia. 34.5	30 dia. 34.5	30 dia. 24.5	30 dia. 24.5	30 dia. 29	32 dia. 37	32 dia. 42.5	32 dia. 43.9
Focal length	6mm	8mm	12mm	16mm	25mm	35mm	50mm	75mm	100mm
Brightness	F1.4	F1.3	F1.4	F1.4	F1.4	F1.9	F1.8	F2.7	F3.5
Filter size	M27 P0.5	M25.5 P0.5	M27 P0.5	M27 P0.5	M27 P0.5	M27 P0.5	M30.5 P0.5	M30.5 P0.5	M30.5 P0.5

Lenses for small camera

Model	FZ-LES3	FZ-LES6	FZ-LES16	FZ-LES30
Appearance	12 dia. 16.4	12 dia. 19.7	12 dia. 23.1	12 dia. 25.5
Focal length	3mm	6mm	16mm	30mm
Brightness	F2.0	F2.0	F3.4	F3.4

Extension Tubes

Model	3Z4S-LE ML-EXR
Contents	Set of 7 tubes(40 mm, 20 mm, 10 mm, 5 mm, 2.0 mm, 1.0 mm, and 0.5 mm) Maximum outer diameter: 30 mm dia.

Extension Tubes for small camera

Model	FZ-LESR
Contents	Set of 3 tubes(15 mm, 10 mm, 5 mm) Maximum outer diameter: 12 mm dia.

[•] Do not use the 0.5-mm, 1.0-mm, and 2.0-mm Extension Tubes attached to each other. Since these Extension Tubes are placed over the threaded section of the Lens or other Extension Tube, the connection may loosen when more than one 0.5-mm, 1.0-mm or 2.0-mm Extension Tube are used together.

[•] Reinforcement may be required for combinations of Extension Tubes exceeding 30 mm if the Camera is subject to vibration.

Ratings and Performance

Controller

Model		NPN Output PNP Output	FJ-3000 FJ-3005	FJ-3000-10 FJ-3005-10	FJ-3050 FJ-3055	FJ-3050-10 FJ-3055-10	FJ-H3000 FJ-H3005	FJ-H3000-10 FJ-H3005-10		FJ-H3050-10 FJ-H3055-10	FJ-350 FJ-355	FJ-350-10 FJ-355-10	
Controller	уре	FINE Output	Controller integ		Box-type c		Controller integ		Box-type of		Box-type c		
No. of cam			2	4	2	4	2	4	2	4	2	4	
CPU			Intel Core i	Intel Core i5-520E Processor 2.40 GHz								Intel Atom N270 Processor 1.6 GHz	
Main memo	orv		3 GB								2 GB	1.6 GHZ	
Storage	,		Compact F	lash 2 GB							_ 0.5		
os			Windows E	mbedded S	tandard 200								
Dual-task						Y	es					lo	
HALCON in Connected			Can be cor	nnected to a	lo ll comoras			Y	es		N	lo	
	Camera				ith LCD: tou	ch pen. moi	use. etc.						
Operation			Box-type c	ontroller: mo	ouse, etc.	•							
Processing	resolution		300,000-pi	xel camera:	mera: 752 (640 (H) × 4 1600 (H) ×	80 (V)) million pixel	camera: 24	88 (H) × 204	14 (V)			
No. of scen	ies		32			(1), 0			,	(.)			
		Connected	214										
	When	to 1 camera											
	connected to	Connected to 2 cameras	107										
	an Intelligent Compact	Connected	71										
	Camera	to 3 cameras	′ '										
		Connected to 4 cameras	53										
		Connected	Color con	ro. 050 M	noob***** - 1	Comers: OF)						
		to 1 camera	Color came	a: ∠50, MC	nochrome (zamera: 252							
	When connected to a 300,000-pixel	Connected to 2 cameras	Color came	era: 125, Mo	nochrome (Camera: 126	3						
	camera	Connected to 3 cameras Connected			ochrome Ca								
Number of logged		to 4 cameras		Color camera: 62, Monochrome Camera: 63									
images	When connected to a 2 million-pixel camera	to 1 camera Connected		Color camera: 40, Monochrome Camera: 40 Color camera: 20, Monochrome Camera: 20									
		to 2 cameras Connected		Color camera: 13, Monochrome Camera: 13									
		to 3 cameras Connected to 4 cameras	Color came	era: 10, Mon	ochrome Ca	amera: 10							
		Connected to 1 camera	Color came	Color camera: 15, Monochrome Camera: 15									
	When connected to a	Connected to 2 cameras	Color camera: 7, Monochrome Camera: 7										
	5 million-pixel camera	Connected to 3 cameras Connected	Color camera: 5, Monochrome Camera: 5										
		to 4 cameras	Color camera: 3, Monochrome Camera: 3										
Serial com	munications		RS-232C/4	22A: 1CH							RS-232C:		
Network co	mmunications		Ethernet 100BASE-TX/10BASE-T							Ethernet 100 100BASE-TX			
EtherNet/IF			Ethernet po	ort baud rate	e: 100 Mbps	(100BASF-	TX)				IOODAGE-IA	V TODASE-	
Parallel I/O			Ethernet port baud rate: 100 Mbps (100BASE-TX) 17 inputs (RESET, STEP0/ENCTRIG_Z0, STEP1/ENCTRIG_Z1, DSA0 to 1, ENCTRIG_A0 to 1, ENCTRIG_B0 to 1, DI0 to 7) 29 outputs (RUN/BUSY1, BUSY0, GATE0 to 1, OR0 to 1, READY0 to 1, ERROR, STGOUT0 to 3*, DO0 to 15) 11 inputs (RESET, STEP, DSA, DI0 to 26 outputs (RUN/BUSY1, BUSY0, GATE0 to 1, OR0 to 1, READY0 to 1, ERROR, STGOUT0 to 3*, DO0 to 15)							A, DIO to N, BUSY, ADY, ERROF *, DO0 to 15)			
Monitor int	erface						ler and LCD channel (Res			(Resolution: 8 dots)	XGA 1,024 >	< 768 dots	
USB interfa	ice		4 channels	(supports L	JSB 1.1 and	2.0)					2 channels USB 1.1 ai		
Power sup	oly voltage		20.4 to 26.	4 VDC							305 I.I al		
Current	When connected to Intelligent Compa intelligent or auto	ct Camera,	5.0 A max.	7.5 A max.	5.0 A max.	7.5 A max.	5.0 A max.	7.5 A max.	5.0 A max.	7.5 A max.	4.0 A max.	5.5 A ma	
consumption (at 24.0 VDC)	When connected to pixel, 2 million-pix	to a 300,000- cel, or 5	3.7 A max.	4.9 A max.	3.7 A max.	4.9 A max.	3.7 A max.	4.9 A max.	3.7 A max.	4.9 A max.	2.6 A max.	2.9 A ma	
	million-pixel came	era	$ \begin{array}{ccc} 0 \text{ to } +45^{\circ}\text{C for low cooling fan speeds} & \text{Storage} \\ 0 \text{ to } +50^{\circ}\text{C for high cooling fan speeds} & \text{(with no} \end{array} $						Operating: Storage: -2 (with no ici condensati	20 to 65°C ng or			
	ımidity range				: 35 to 85°C	,		4 1	A	0.1	A	2.1	
Weight			Approx. 3.4		Approx. 1.9		Approx. 3.4		Approx. 1.		Approx. 1.8		
Weight Accessories			Controller integrated with LCD: touch pen (one, inside the front panel), Instruction Manual, 6 mounting brackets, Member registration sheet Box-type controller: Instruction Manual, Member registration sheet										

^{*} STGOUT 2 to 3 only for camera 4ch type

Digital Cameras

	FZ-S	FZ-SC	FZ-S2M	FZ-SC2M	FZ-S5M2	FZ-SC5M2
Image elements	Interline transfer read CCD image elements	ling all pixels, 1/3-inch	Interline transfer readii CCD image elements	ng all pixels, 1/1.8-inch	Interline transfer readi CCD image elements	ng all pixels, 2/3-inch
Color/Monochrome	Monochrome	Color	Monochrome	Color	Monochrome	Color
Effective pixels	640 (H) × 480 (V)		1600 (H) × 1200 (V)		2448 (H) × 2044 (V)	
Pixel size	$7.4 (\mu m) \times 7.4 (\mu m)$		4.4 (μm) × 4.4 (μm)		3.45 (μm) × 3.45 (μm)	
Shutter function	Electronic shutter; select shutter speeds from 1/10 to 1/50,000 s		Electronic shutter; select shutter speeds from 1/10 to 1/50,000 s		Electronic shutter; select shutter speeds from 1/10 to 1/50,000 s	
Partial function	12 to 480 lines		12 to 1200 lines		12 to 2044 lines	
Frame rate (image read time)	80 fps (12.5 ms)		30 fps (33.3 ms)		16 fps (62.5 ms)	
Field of vision, installation distance	Selecting a lens acco	Selecting a lens according to the field of vision and installation distance				
Ambient temperature range	Operating: 0 to 50°C Storage: -25 to 65°C (with no icing or condensation)		Operating: 0 to 40°C Storage: -25 to 65°C (with no icing or condensation)		Operating: 0 to 40°C Storage: -25 to 65°C (with no icing or condensation)	
Ambient humidity range	Operating and storage: 35% to 85% (with no condensation)					
Weight	Approx. 55 g		Approx. 76 g		Approx.140 g	
Accessories	Instruction manual					

Small Digital Cameras

	FZ-SF	FZ-SFC	FZ-SP	FZ-SPC	
Image elements	Interline transfer	Interline transfer reading all pixels, 1/3-inch CCD image elements			
Color/Monochrome	Monochrome	Color	Monochrome	Color	
Effective pixels	640 (H) × 480 (V	")			
Pixel size	$7.4 (\mu m) \times 7.4 (\mu$	ım)			
Shutter function	Electronic shutte	r; select shutter sp	peeds from 1/10 to	o 1/50,000 s	
Partial function	12 to 480 lines				
Frame rate (image read time)	80 fps (12.5 ms)				
Field of vision, installation distance	Selecting a lens according to the field of vision and installation distance				
Ambient temperature range	e Operating: 0 to 50°C (camera amp) Operating: 0 to 50°C (c of to 45°C (camera head) Oto 45°C (camera head) Storage: -25 to 65°C (with no icing or condensation) icing or condensation)		ra head) 55°C (with no		
Ambient humidity range			Operating and st 85% (with no cor		
Weight	Approx.150 g Appro		Approx.150 g		
Accessories	Instruction manu bracket, Four mo brackets(M2)		Instruction manu	ıal	

High-speed Cameras

	FZ-SH	FZ-SHC	
Image elements	Interline transfer r 1/3-inch CCD ima		
Color/Monochrome	Monochrome	Color	
Effective pixels	640 (H) × 480 (V)	
Pixel size	$7.4 (\mu m) \times 7.4 (\mu m)$	ım)	
Shutter function	Electronic shutter; select shutter speeds from 1/10 to 1/50,000 s		
Partial function	12 to 480 lines		
Frame rate (image read time)	204 fps (4.9 ms)		
Field of vision, installation distance	Selecting a lens according to the field of vision and installation distance		
Ambient temperature range	Operating: 0 to 40°C Storage: -25 to 65°C (with no icing or condensation)		
Ambient humidity range	Operating and storage: 35% to 85% (with no condensation)		
Weight	Approx.105 g		
Accessories	Instruction manual		

Intelligent Compact Cameras

	FZ-SQ010F	FZ-SQ050F	FZ-SQ100F	FZ-SQ100N		
		FZ-5Q050F	F2-5Q100F	F2-5Q100N		
Image elements	1/3-inch CMOS image elements					
Color/Monochrome	Color					
Effective pixels	752 (H) × 480 (V)					
Pixel size	6.0 (μm) × 6.0 (μm)					
Shutter function	1/250 to 1/32,258	1/250 to 1/32,258				
Partial function	8 to 752 lines					
Frame rate (image read time)	60 fps	60 fps				
Field of vision	7.5 × 4.7 to 13 × 8.2 mm	13 × 8.2 to 53 × 33 mm	53 × 33 to 240 × 153 mm	29 × 18 to 300 × 191 mm		
Installation distance	38 to 60 mm	56 to 215 mm	220 to 970 mm	32 to 380 mm		
LED class	Class 2	Class 2				
Ambient temperature range	Operating: 0 to 50°C Storage: -25 to 65°C					
Ambient humidity range	Operating and storage: 35% to 85% (with no condensation)					
Weight	Approx. 150 g Approx. 140 g					
Accessories	Mounting bracket (FQ-XL), polariz	ing filter attachment (FQ-XF1),	instruction manual and warning label			

Intelligent Cameras, Autofocus Cameras

_	FZ-SLC100	FZ-SLC15	FZ-SZC100	FZ-SZC15
Image alamanta			12-320100	12-32013
Image elements	Interline transfer reading all pixels	1/3-inch CCD image elements		
Color/Monochrome	Color			
Effective pixels	640 (H) × 480 (V)			
Pixel size	7.4 (μm) × 7.4 (μm)			
Shutter function	Electronic shutter; select shutter s	peeds from 1/10 to 1/50,000 s		
Partial function	12 to 480 lines			
Frame rate (image read time)	80 fps (12.5ms)			
Field of vision (See note 2.)	13 to 100 mm (See note1.)	2.9 to 14.9 mm (See note1.)	13 to 100 mm (See note1.)	2.9 to 14.9 mm (See note1.)
Installation distance	70 to 190 mm (See note1.)	35 to 55 mm (See note1.)	77.5 to 197.5 mm (See note1.)	47.5 to 67.5 mm
LED class (See note 3.) (lighting)	Class 2			_
Ambient temperature range	Operating: 0 to 50°C Storage: -25 to 65°C (with no icing or condensation)			
Ambient humidity range	Operating and storage: 35% to 85% (with no condensation)			
Weight	Approx. 670 g	Approx. 700 g	Approx. 500 g	
Accessories	Instruction Sheet and hexagonal wrench			

Note: 1. Tolerance: ±5% max.
2. The length of the visual field is the lengths along the Y axis.
3. Applicable standards: IEC 60825-1: 1993 + A1: 1997 + A2-2001, EN 60825-1: 1994 + A1: 2002 + A2: 2001

LCD Monitor

	FZ-M08
Size	8.4 inches
Туре	Liquid crystal color TFT
Resolution	1,024 × 768 dots
Input signal	Analog RGB video input, 1 channel
Power supply voltage 21.6 to 26.4 VDC	
Current consumption	Approx. 0.7 A max.
Ambient temperature range	Operating: 0 to 50°C Storage: -25 to 65°C (with no icing or condensation)
Ambient humidity range	Operating and storage: 35 to 85% (with no condensation)
Weight	Approx. 1.2 kg
Accessories	Instruction Sheet and 4 mounting brackets

Camera Cables

	FZ-VS (2 m)	FZ-VSB (2 m)	FZ-VSL (2 m)
Shock resistiveness (durability)	10 to 150 Hz single amplitude 0.15 mm 3 directions, 8 strokes, 4 times		
Ambient temperature range	Operation and storage: 0 to +65°C (with no icing or condensation)		
Ambient humidity range	Operation and storage: 40 to 70%RH (with no condensation)		
Ambient atmosphere	No corrosive gases		
Material	Cable sheath, connector: PVC		
Minimum bending radius	69 mm	81 mm	69 mm
Weight	approx. 170 g	approx. 220 g	approx. 170 g

Monitor Cable

	FZ-VM
Vibration resistiveness	10 to 150 Hz single amplitude 0.15 mm 3 directions, 8 strokes, 4 times
Ambient temperature range	Operation: 0 to +50°C; Storage: -20 to +65°C (with no icing or condensation)
Ambient humidity range	Operation and storage: 35 to 85%RH (with no condensation)
Ambient atmosphere	No corrosive gases
Material	Cable sheath: heat-resistant PVC Connector: PVC
Minimum bending radius	75 mm
Weight	approx. 170 g

Halation Cut Illumination General specifications

	FZ-SXC RB7018BR-4S	FZ-LTC RB7018BR-4S	FZ-LT RB7018BR-4S
Current consumption	18 W or less (12 VDC, 1.5 A max.) (including camera and strobe controller)		
Vibration resistance	10 to 150 Hz single amplitude 0.35 mm (maximum acceleration 50m/s²) 3 directions, 8 strokes, 10 times		
Impact resistance	150m/s ² 6 directions, 3 times		
Ambient temperature	Operating: 0 to 50°C Storage: -25 to 60°C (with no icing or condensation)		
Ambient humidity	Operation and storage: 35 to 85%RH (with no condensation)		
Ambient atmosphere	No corrosive gases		
Protective structure	IEC60259 IP20		
Material	Case: zinc-coated steel plate Cover: acrylic board Clasp: stainless steel plate		
Weight including cables	Approx. 600 g Approx. 500 g Approx. 400 g		

Cable Extension Unit

	FZ-VSJ
Power supply voltage (See note 1.)	11.5 to 13.5 VDC
Current consumption (See note 2.)	1.5 A max.
Ambient temperature range	Operating: 0 to 50°C Storage: -25 to 65°C (with no icing or condensation)
Ambient humidity range	Operating and storage: 35 to 85% (with no condensation)
Maximum Units connectable	2 Units per Camera
Weight	Approx. 240 g
Accessories	Instruction Sheet and 4 mounting screws

Note: 1. A power supply must be connected to the Strobe Controller and Camera when connecting a FZ-SLC100/SLC15/SZC100/SZC15 and using a Strobe Controller (3Z4S-LT MLEK-C100E1TS2.)

2. The current consumption is when every Camera and Strobe Controller is connected to a power supply.

Long-distance Camera Cables

	FZ-VS2 (15 m)	FZ-VSL2 (15 m)	
Shock resistiveness (durability)	10 to 150 Hz single amplitude 0.15 mm 3 directions, 8 strokes, 4 times		
Ambient temperature range	Operation and storage: 0 to +65°C (with no icing or condensation)		
Ambient humidity range	Operation and storage: 40 to 70%RH (with no condensation)		
Ambient atmosphere	No corrosive gases		
Material	Cable sheath, connector: PVC		
Minimum bending radius	93 mm		
Weight	approx. 1600 g		

Parallel Cable

	FZ-VP	FZ-VPX	
Vibration resistiveness	10 to 150 Hz single amplitude 0.15 mm 3 directions, 8 strokes, 4 times		
Ambient temperature range	Operation: 0 to +50°C; Storage: -20 to +65°C (with no icing or condensation)		
Ambient humidity range	Operation and storage: 35 to 85%RH (with no condensation)		
Ambient atmosphere	No corrosive gases		
Material	Cable sheath: heat-resistant PVC Connector: resi		
Minimum bending radius	75 mm		
Weight	approx.160 g	approx.180 g	

Illumination specifications

	Specifications		
Source	Blue LED (wavelength: Approx. 470 nm) Red LED (wavelength: 630 nma)		
Illumination system	8 blocks luminous intensity variable illumination		
Average lifetime	5,000 hours (Time it takes from manufacture for a 50% reduction in luminous intensity at an ambient temperature of 25°C, maximum brightness, and continuous illumination.)		

Cameras / Cables Connection Table

Type of camera	Model	Cable length	Intelligent cameras Autofocus cameras	High-speed cameras	Digital cameras			Small digital cameras	Intelligent compact
Type of Camera					300,000-pixel	2 million-pixel	5 million-pixel	Pen type / flat type	cameras
Camera Cables Right-angle camera cables	FZ-VS FZ-VSL	2m	Yes	Yes	Yes	Yes	Yes	Yes	Yes
		5m	Yes	Yes	Yes	Yes	Yes	Yes	Yes
		10m	No	Yes	Yes	Yes	No	Yes	Yes
Bend resistant camera cables	FZ-VSB	2m	Yes	Yes	Yes	Yes	Yes	Yes	Yes
		5m	Yes	Yes	Yes	Yes	Yes	Yes	Yes
		10m	No	Yes	Yes	No	No	Yes	Yes
Long-distance camera cable Long-distance right-angle camera cable	FZ-VS2 FZ-VSL2	15m	No	Yes	Yes	Yes	No	Yes	Yes

Processing Items

*The red items are available only with controllers with HALCON. Group Icon Processing Item Search Used to identify the shapes and calculate the position of measurement objects. Flexible Search Recognizing the shapes of workpieces with variation and detecting their positions. Sensitive Search Search a small difference by dividing the search model in detail, and calculating the correlation. **ECM Search** Used to search the similar part of model form input image. Detect the evaluation value and position. Ec Circle Search Extract circles using "round " shape information and get position, radius and quantity in high preciseness. Shape Search+ Used to Search the similar part of models from input image. Detect the evaluation value and position. 0 Classification Used when various kinds of products on the assembly line need to be sorted and identified. **Edge Position** Measure position of measurement objects according to the color change in measurement area. Edge Pitch Detect edges by color change in measurement area. Used for calculating number of pins of IC and connectors. 1111 Measure peak/bottom edge position of workpieces according to the color change in separated measurement # Scan Edge Position area Measure max/min/average width of workpieces according to the color change in separated measurement 邕 Scan Edge Width area Color Data Used for detecting presence and mixed varieties of products by using color average and deviation. s. Inspections / 1 Gravity and Area Used to measure area, center of gravity of workpieces by extracting the color to be measured. Measurement Labeling Used to measure number, area and gravity of workpieces by extracting registered color. Selecting one region of extracted Labeling, and get that measurement. Area and Gravity position can be got 4 Label Data and judged. Labeling+ Extract objects of registered color, and measure many features such as number and circularity. Defect Used for appearance measurement of plain-color measurement objects such as defects, stains and burrs. A PreciseDefect Check the defect on the object. Parameters for extraction defect can be set precisely. Fine Matching Difference can be detected by overlapping and comparing(matching) registered fine images with input images. Character Inspection Recognize character according correlation search with model image registered in [Model Dictionary]. AB Bate (0) 62-1 Date Verification Reading character string is verified with internal date. Model Dictionary Register character pattern as dictionary. The pattern is used in [Character Inspection]. Barcode+ HIII Recognize barcode, verify and output decoded characters. (See note 1) Recognize 2D code, verify and output decoded characters. 艇 (See note 2) Circle Angle Used for calculating angle of inclination of circular measurement objects. **(** Camera Image Input To input images from cameras. And set up the conditions to input images from cameras. Camera Image Input Create high-dynamic range images by acquiring several images with different conditions. **HDR** Image Camera Image Input HDR function for FZ-SQ□ Intelligent Compact Cameras. HDR Lite Capturing

Note: 1. Bar Codes that can be read: JAN/EAN/UPC (including add-on codes), Code 39, Codabar (NW-7), ITF (Interleaved 2 of 5), Code 93, Code 128, GS1-128, GS1 DataBar (RSS-14 / RSS Limited / RSS Expanded), Pharmacode

Rectify the trapezoidal deformed image.

To switch the cameras used for measurement. Not input images from cameras again.

Used when positions are differed. Correct measurement is performed by correcting position of input images.

Used for processing images input from cameras in order to make them easier to be measured.

To switch the images used for measurement. Not input images from camera again.

2. 2D Codes that can be read : Data Matrix (ECC200), QR Code

Camera Switching

Switching

Trapezoidal

Correction+

Filtering

20

Measurement Image

Position Compensation

Correcting

images

Group	Icon	*The red items are available only with controllers with HALCON. Processing Item					
эхээр		Background Suppression	To enhance contrast of images by extracting color in specified brightness.				
Correcting images	4	Color Gray Filter	Color image is converted into monochrome images to emphasize specific color.				
	-	Extract Color Filter	Convert color image to color extracted image or binary image.				
	-	Anti Color Shading	To remove the irregular color/pattern by uniformizing max.2 specified colors.				
	=	Stripes Removal Filter+	Remove the background pattern of stripes.				
	10	Halation Cut+	Remove halation from input image.				
		Panorama+	Combine multiple image to create one big image.				
	EN ELL	Polar Transformation	Rectify the image by polar transformation. Useful for OCR or pattern inspection printed on circle.				
	00	Macro	Advanced arithmetic processing can be easily incorporated into workflow as macro processing items.				
		Calculation	Used when using the judge results and measured values of ProcItem which are registered in processing units.				
	**	Line Regression	Used for calculating regression line from plural measurement coordinate.				
-	0	Circle Regression	Used for calculating regression circle from plural measurement coordinate.				
		Calibration+	Transform (X,Y) position to the real coordinate system.				
	4	Set Unit Data	Used to change the ProcItem data (setting parameters,etc.) that has been set up in a scene.				
	file:	Get Unit Data	Used to get one data (measured results, setting parameters,etc.) of ProcItem that has been set up in a scene.				
Assisting inspections /	4	Set Unit Figure	Used for re-setting the figure data (model, measurement area) registered in an unit.				
measurement	(Get Unit Figure	Used for get the figure data (model, measurement area) registered in an unit.				
		Trend Monitor	Used for displaying the information about results on the monitor, facilitating to avoid NG and analyze causes.				
	第二	Image Logging	Used for saving the measurement images to the memory and USB memory.				
	五二	Data Logging	Used for saving the measurement data to the memory and USB memory.				
	٥	Elapsed Time	Used for calculating the elapsed time since the measurement trigger input.				
	互	Wait	Processing is stopped only at the set time. The standby time is set by the unit of [ms].				
	4	Focus	Focus setting is supported.				
	*	Iris	Focus and aperture setting is supported.				
Branching processing	80	Conditional Branch	Used where more than two kinds of products on the production line need to detected separately.				
	40	End	This ProcItem must be set up as the last processing unit of a branch.				
	To.	DI Branch	Same as ProcItem "Branch". But you can change the targets of conditional branching via external inputs.				
Outputting results	11	Data Output	Used when you need to output data to the external devices such as PLC or PC via serial ports.				
		Parallel Data Output	Used when you need to output data to the external devices such as PLC or PC via parallel ports.				
	15	Parallel Judgement Output	Used when you need to output judgement results to the external devices such as PLC or PC via parallel ports.				
	1	Fieldbus Data Output	Outputs data to an external device, such as a Programmable Controller, through a fieldbus interface.				
Disalasi		Result Display	Used for displaying the texts or the figures in the camera image .				
Displaying results on the monitor	2	Display Image File	Display selected image file.				
	-	Display Last NG Image	Display the last NG images.				

Controllers


■ LCD-integrated type

FJ-300□/FJ-300□-10 FJ-H300□/FJ-H300□-10


20 Four, M3 mounting holes a depth of 6 mm The size of the 2-camera type is 83.

■ Box-type

FJ-305□/FJ-305□-10 FJ-H305□/FJ-H305□-10




FJ-35 | /FJ-35 | -10




Cable **Camera Cable**

■ Camera Cable(Model FZ-VS)


■ Long-distance Camera Cable(Model ■ Bend resistant Cable(Model FZ-FZ-VS2)




VSB)



■ Long-distance Right-angle Camera Cable(Model FZ-VSL2) ■ Right-angle Camera Cable(Model FZ-VSL)






[Note1]:cable is available in 2m/5m/10m. [Note2]:Each camera cables has polarity. Please ensure that the name plate side of the cable is connected to the controller. [Note3]:cable is available in 15m.


Parallel Cable(Model FZ-VP)

FZ-VP

FZ-VPX

(100) 50-pin square connecto





Monitor Cable(Model FZ-VM)

[Note1]:cable is available in 2m/5m.


[Note1]: cable is available in 2m/5m.

[Note1]:cable is available in 2m/5m.


Cameras

■ Digital cameras


300,000-pixel camera FZ-S FZ-SC



2 million-pixel camera FZ-S2M FZ-SC2M



5 million-pixel camera FZ-S5M2 FZ-SC5M2





■ Small digital cameras

Camera head

Flat camera FZ-SF **FZ-SFC**


Pen-shaped camera FZ-SP **FZ-SPC**






Camera amplifier

Can be used for both flat cameras and pen-shaped cameras



■ High speed camera

FZ-SHC FZ-SH



Tightening torque: 1.2 N·m


■ Intelligent Compact Cameras

Narrow view / Standard FZ-SQ010F FZ-SQ050F Wide View FZ-SQ100F (long-distance) FZ-SQ100N (short-distance) Mounting Bracket 4-M4 Depth: 6 Mounting Hole Dimensions Mounting Hole Dimensions


[Note1]: The mounting brackets can be connected to either si

See the diagram below when mounting bracket FQ-XL2 is attached.

[Note1]: The mounting brackets can be connected to either side




■ Intelligent camera




■ Auto focus camera

FZ-SZC15 FZ-SZC100




Lens for small camera

FZ-LES Series



LensesModel	Focal length	Brightness	Maximum outside diameter	Overall length
FZ-LES3	3mm	F2.0	12 dia.	16.4mm
FZ-LES6	6mm	F2.0	12 dia.	19.7mm
FZ-LES16	16mm	F3.4	12 dia.	23.1mm
FZ-LES30	30mm	F3.4	12 dia.	25.5mm

Extension Tubes for small camera FZ-LESR





Special Halation-cutoff Lamp

FZ-SXCRB7018BR-4S (camera-integrated type)













Installation dimensions

Camera Cable Extension Unit FZ-VSJ




LCD Monitor FZ-M08




Optical Chart

5 million-pixel digital camera FZ-S□5M2




The 5-mm Extension Tubes (3Z4S-LE ML-EXR) cannot be used with FZ-LEH25 Lenses.

2 million-pixel digital camera FZ-S□2M




The 5-mm Extension Tubes (3Z4S-LE ML-EXR) cannot be used with FZ-LEH25 Lenses.

300,000-pixel High-speed camera FZ-SH \square , and Digital camera FZ-S \square




300,000-pixel small digital cameras FZ-SF□, FZ-SP□



Note: 1. The vertical axis represents WD, not installation distance.

■ Meaning of Optical Chart

The X axis of the optical chart shows the field of vision (mm)(Note1), and the Y axis of the optical chart shows the camera installation distance (mm)(Note2).



Note: 1. The lengths of the fields of vision given in the optical charts are the lengths of the Y axis.


2. The vertical axis represents WD for small cameras.


Intelligent Cameras, Autofocus Cameras

■ Narrow View (Unit: mm)

FZ-SLC15

FZ-SZC15







■ Wide View

FZ-SLC100

FZ-SZC100







* Field of Vision of Intelligent Cameras and Autofocus Cameras The images displayed on the monitor will be rectangular images of 640×480 pixels. The valid processing area for measurements is the 480×480-pixel area in the middle. The above figures show the dimensions of the middle 480×480 pixels.


Intelligent Compact Cameras
■ Narrow View ■ Standard


FZ-SQ010F FZ-SQ050F FZ-SQ100F

■ Wide View (Long-distance) ■ Wide View (Short-distance) FZ-SQ100N









ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. Q184-E1-01A

In the interest of product improvement, specifications are subject to change without notice.