

# **OMRON TM Collaborative Robot, S Series**

# TM S Series

# S Series Collaborative Robot (Cobot) for assembly, palletizing, inspection, logistics and many other applications

- Designed to promote a safe and harmonious workplace between humans and machines.
- 31 safety functions, all ISO 13849-1, Cat.3, PLd, certified.
- Full ISO 10218-1 compliance.
- Easy-to-use graphical programming environment for quick startup and operation.
- Built-in vision-based robot control enables visual servoing, inspection, and measurement operations.
- Optional camera and Landmark allows for truly flexible, fast changeover.
- Capability to integrate with mobile robots enables fully autonomous machine tending and logistics handling applications.



## **Part Number Structure**

### RT6 - 000000

1 2 3 4 5 6 7 8

No.	Item	Specifications	Symbol
1		TMS Series	6
		TM5S	0
2	Model Type	TM7S	6
2	Model Type	TM12S	1
		TM14S	2
3	Power Source	AC	0
3	rowel Source	DC *1	1
4	Vision	Standard Model with Integrated Camera	0
-	VISIOII	X Model without Camera	1
	Arm Length (mm)	700 (TM7S)	70
<b>500</b>		900 (TM5S)	90
5 & 6		1300 (TM12S)	13
		1100 (TM14S)	11
		Standard	0
7	Ontion	SEMI	1
,	Option	Fieldbus	2
		SEMI, Fieldbus	5
•	Cable Length (m)	Standard Length (1.5 for DC unit / 3 for AC unit)	4
8	Cable Length (m)	Extended Length (3 for DC unit /12 for AC unit)	5

<sup>\*1.</sup> DC powered Cobots are capable of mobile operation when paired with an Autonomous Mobile Robot.

# **Ordering Information**

# **Standard Units Ordering Information**

Product Model	Maximum Payload (kg)	Reach (mm)	Integrated Camera	Extended Cable *1	DC Power Source *2	SEMI S2 Certified *3	Global P/N
TM5S			Yes	No	No		RT6-0009004
TM5S, 12 m cable			168	Yes			RT6-0009005
TM5S-X	5	900	No	No		No	RT6-0019004
TM5S-X, 12 m cable	3	900	140	Yes		140	RT6-0019005
TM5S-M			Yes	No	Yes		RT6-0109004
TM5S-M, 3 m cable			163	Yes	163		RT6-0109005
TM7S			Yes	No			RT6-6007004
TM7S, 12 m cable			165	Yes	No	No	RT6-6007005
TM7S-X	7	700	No Yes	No	Yes		RT6-6017004
TM7S-X, 12 m cable				Yes			RT6-6017005
TM7S-M				No			RT6-6107004
TM7S-M, 3 m cable			163	Yes			RT6-6107005
TM12S			Yes	No	- No	No	RT6-1001304
TM12S, 12 m cable				Yes			RT6-1001305
TM12S-X			No	No			RT6-1011304
TM12S-X, 12 m cable	12	1300	140	Yes		INO	RT6-1011305
TM12S-M				No			RT6-1101304
TM12S-M, 3 m cable			Yes	Yes	Yes		RT6-1101305
TM12S-M SEMI				No		Yes	RT6-1101314
TM14S			Yes	No			RT6-2001104
TM14S, 12 m cable			103	Yes	No		RT6-2001105
TM14S-X			No	No	140	No	RT6-2011104
TM14S-X, 12 m cable	14	1100	INO	Yes		INO	RT6-2011105
TM14S-M				No			RT6-2101104
TM14S-M, 3 m cable			Yes	Yes	Yes		RT6-2101105
TM14S-M SEMI				No		Yes	RT6-2101114

<sup>\*1.</sup> The default cable length is 1.5 m for DC units and 3 m for AC units. The extended cable length is 3 m for DC units and 12 m for AC Units.

<sup>\*2.</sup> Standard Omron Cobots use AC as the power source. DC powered cobots are capable of mobile operation when paired with an Autonomous Mobile Robot.

<sup>\*3.</sup> SEMI (Semiconductor Equipment and Materials International) is the central global network of manufacturers of micro and nano electronics that issues safety guidelines. SEMI S2 is the most well-known standard in semiconductor manufacturing equipment for Environmental, Health, and Safety (EHS).

# **Fieldbus Units Ordering Information**

Product Model	Maximum Payload (kg)	Reach (mm)	Integrated Camera	Extended Cable *1	DC Power Source *2	SEMI S2 Certified *3	Global P/N
TM5S, Fieldbus			Yes	No	- No		RT6-0009024
TM5S, 12 m cable, Fieldbus				Yes			RT6-0009025
TM5S-X, Fieldbus	5	900	No	No		No	RT6-0019024
TM5S-X, 12 m cable, Fieldbus	3	900	INU	Yes		NO	RT6-0019025
TM5S-M, Fieldbus			Yes	No	Yes		RT6-0109024
TM5S-M, 3 m cable, Fieldbus			163	Yes	163		RT6-0109025
TM7S, Fieldbus			Yes	No			RT6-6007024
TM7S, 12 m cable, Fieldbus			res	Yes	No	No	RT6-6007025
TM7S-X, Fieldbus	7	700	No	No	Yes		RT6-6017024
TM7S-X, 12 m cable, Fieldbus	,	700	140	Yes			RT6-6017025
TM7S-M, Fieldbus			Yes	No			RT6-6107024
TM7S-M, 3 m cable, Fieldbus			103	Yes			RT6-6107025
TM12S, Fieldbus			Yes	No	- No	No	RT6-1001324
TM12S, 12 m cable, Fieldbus				Yes			RT6-1001325
TM12S-X, Fieldbus			No	No			RT6-1011324
TM12S-X, 12 m cable, Fieldbus	12	1300	110	Yes		NO	RT6-1011325
TM12S-M, Fieldbus				No			RT6-1101324
TM12S-M, 3 m cable, Fieldbus			Yes	Yes	Yes		RT6-1101325
TM12S-M SEMI, Fieldbus				No		Yes	RT6-1101354
TM14S, Fieldbus			Yes	No			RT6-2001124
TM14S, 12 m cable, Fieldbus			165	Yes	No		RT6-2001125
TM14S-X, Fieldbus			No	No		No	RT6-2011124
TM14S-X, 12 m cable, Fieldbus	14	1100	110	Yes		NO -	RT6-2011125
TM14S-M, Fieldbus				No			RT6-2101124
TM14S-M, 3 m cable, Fieldbus			Yes	Yes	Yes		RT6-2101125
TM14S-M SEMI, Fieldbus				No		Yes	RT6-2101154

<sup>\*1.</sup> The default cable length is 1.5 m for DC units and 3 m for AC units. The extended cable length is 3 m for DC units and 12 m for AC Units.

# Items Included with an S Series Cobot System

Item	Cobot	Cable	Robot Stick	Control Box	Calibration Plates	I/O Cables	Landmark	Ground wire	Jumper Wire	Power cable	SEMI Switch	SEMI ESTOP Cable
Description	TM5S, TM7S, TM12S, TM14S	3, 1.5, and 12 m options	Hand control to move cobot	Robot Control Box	Large plate	1 m	Not compatible with X model cobots	3 m	3 cm	For Control Box (3 cable: B, G, F) 1.8 m	SEMI Emergency OFF, SEMI cobots only	SEMI cobots only, 3 m
Quantity	1	1	1	1	1	1	2	2	2	1	1	1

<sup>\*2.</sup> Standard Omron Cobots use AC as the power source. DC powered cobots are capable of mobile operation when paired with an Autonomous Mobile Robot.

<sup>\*3.</sup> SEMI (Semiconductor Equipment and Materials International) is the central global network of manufacturers of micro and nano electronics that issues safety guidelines. SEMI S2 is the most well-known standard in semiconductor manufacturing equipment for Environmental, Health, and Safety (EHS).

# **Accessories And Optional Items**

Appearance	Product Name	Description	Remarks	Part Number
omron / \tau \tau \tau	Landmark	Robot positioning tool as a reference to the environment.	Two included with purchase of a cobot. Not included with X model cobots	RT6-A000021
	Mobile Workstation (MWS)	MWS is a convenient tool for users to mount the cobot arm on work surface, and store the control box safely within. Users can easily move the MWS with the cobot to different work cells.	Compatible with OMRON TM5S, TM7S, TM5-700, and TM5-900.	RT6-A000010
	Robot stand	Similar to MWS, the robot stand can be easily moved with the cobot to different work stations.	Compatible with OMRON TM5S, TM7S, TM5-700, and TM5-900.	RT6-A000009
- SA	SSD with cable	128 GB solid state hard drive.	SATA cable included. Recommended for external cameras image logging.	RT6-A000012
12	Kit, calibration set with additional pin	Toolkit for teaching a precise tool center point (TCP) that can be used for manual workspace calibration within TMvision.	Required for TCP and manual vision calibration.	RT6-A000002
	Polarizer Light Module, S Series	Improves the reflection caused by the cobot's own light source on the surface of highly reflective objects.	For S Series Cobots only.	RT6-A000025
	Air Filter (ROHS)	Replacement air filter for the control box.	The filter must be changed regularly to maintain efficiency. The replacement procedure can be found in the Hardware Installation Manual.	19937-214F
* l	TM Screen (Teaching Pendant) with Pen	The TM Screen devices can be combined with the Robot Stick design to become a teaching pendant, and operate the cobot from the touch screen environment.	The TM Screen is only compatible with S Series units. No additional wiring is needed.	RT6-A000024

# **Software**

Product Name	Add-On Product Names	Remarks	Part Number
TMflow	N/A	Software required to control the cobot. Free download	N/A
	USB dongles with below softw		
Super Software Dongle	TM Identify & Measure	License, add-on to TMflow. Includes: identification of pose variation, specific color area size, subtract reference image, line/circle burr, counting and gauge.	RT6-A000026
	TM External Vision	External Vision License, add-on to TMflow. Required when using eye-to-hand cameras.	
	TM OCR	License, add-on to TMflow. Includes: Text OCR and Number OCR.	

# **Specifications**


	Product	TM5S	TM7S	TM12S	TM14S		
Weight (With Camera / k	g)	23.9	22.9	33.3	33		
Weight (Without Camera	/ kg)	23.6	22.6	33	32.7		
Maximum payload (kg)		5	7	12	14		
Reach (mm)		900	700	1300	1100		
Mounting			Wall, Ta	ble, Ceiling	•		
Joint ranges	J1, J2, J4, J5, J6		360°				
Joint ranges	J3	±158°	±152°	±162°	±163°		
	J1, J2	18	80°/s	12	0°/s		
Joint speed	J3	18	80°/s	18	0°/s		
Joint Speed	J4, J5	225°/s		22	5°/s		
	J6	450°/s		450°/s			
Average speed (m/s)		1.4	1.1	1.3	1.1		
Repeatability (mm)		±0.03					
Degrees of freedom		6 rotating joints					
	Control Box	Digital In: 16 / Digital Out: 16					
I/O Ports		Analog In: 2 / Analog Out: 2					
	Tool Conn.	Digital In: 3 / Digital Out: 3					
I/O power supply		24 V 2.0 A for control box and 24 V 1.0 A for tool					
Ingress Protection		IP54 for Robot Arm, AC control Box, Robot Stick and TM Screen					
Cleanroom Class		ISO Class 3					
Operating Temperature	and Humidity	0 to 50°C, 85% max. (with no condensation)					
Motor Power Supply		100 to 240 VAC, 50/60 HZ for AC Units; 24 to 60 VDC for DC units					
I/O Interface		2 × COM, 1 × HDMI, 3 × LAN, 2 × USB 2.0, 4 × USB 3.0					
Communication		RS232, Ethernet, Modbus TCP/RTU (master & slave)					
		PROFINET (optional), EtherNet/IP (optional)					
Programming Environm	ent	TMflow, flowchart based and script based					
Certification		SEMI S2 (optional)					
Robot Vision	Eye in Hand (Built in)	1.2 M / 5 M pixels, color camera (camera models only)					
TODOL VISION	Eye to Hand (Optional)	Support Maximum 2 GigE 2D cameras					


**Dimensions** 


## TM7S/TM7S-X/TM7S-M \*

# 131.50 134.95 00.882 00.882 00.882 00.882 00.882 00.882

#### TM5S/TM5S-X/TM5S-M \*









<sup>\*</sup> Dimensions do not include the camera. Refer to the *Camera Flange dimensions* on page 8 for more information.


#### TM12S/TM12S-X/TM12S-M \*

# 131.50 134.95

#### TM14S/TM14S-X/TM14S-M \*








<sup>\*</sup> Dimensions do not include the camera. Refer to the Camera Flange dimensions on page 8 for more information.


#### Footprint (TM5S/7S Models)

# 


#### Footprint (TM12S/14S Models)



**Control Box** 



**Camera Flange** 



# **Related Manuals**

Catalog Number	Title
1686	Omron TM Collaborative Robot S Series: TM5S and TM7S Hardware Installation Manual
1687	Omron TM Collaborative Robot S Series: TM12S and TM14S Hardware Installation Manual
1688	Omron TM Collaborative Robot S Series: Safety Manual
1689	Omron TM Collaborative Robot: Software Manual TMFlow, Version 2
1690	Omron TM Collaborative Robot: TMVision Software Manual, Version 2
1691	Omron TM Collaborative Robot S Series: Touch Screen User's Manual
1628	Omron TM Collaborative Robot: Mobile Work Station User's Manual
1629	Omron TM Collaborative Robot: Robot Stand User's Manual
1664	Omron TM Collaborative Robot: TMScript Language Manual

МЕМО

# **Terms and Conditions Agreement**

#### Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

#### Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

### **Programmable Products.**

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

#### **Errors and Omissions.**

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

#### **OMRON Corporation** Industrial Automation Company

Kyoto, JAPAN Contact: www.ia.omron.com

#### Regional Headquarters

OMRON EUROPE B.V.
Wegalaan 67-69, 2132 JD Hoofddorp
The Netherlands
Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON ROBOTICS AND SAFETY TECHNOLOGIES, INC.

4225 Hacienda Drive, Pleasanton, CA 94588 U.S.A. Tel: (1) 925-245-3400 Fax: (1) 925-960-0590

OMRON (CHINA) CO., LTD.
Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

**Authorized Distributor:** 

©OMRON Corporation 2023 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM\_1\_1

Cat. No. I889-E-01 0923 (0423)