Indicator (Cylindrical 16-dia.)

CSM\_M16\_DS\_E\_7\_8

# Cylindrical 16-dia. Indicator


• Same basic design as the A16 Pushbutton Switch.




Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions on page 10.

## List of Models

	Appearance	Model
Solder terminals	Rectangular	M16-J
	Square	M16-A
	Round	M16-T
Voltage- reduction lighting		M16-□
Screw-less Clamp		M16-□






## **Model Number Structure**

**Model Number Legend** ..... The model numbers used to order sets of Units are illustrated below. One set comprises the Display, Case, LED, and Socket.

For information on combinations, refer to Ordering Information on the following pages.



the Display, Case, Lamp, and Socket. Not all combinations are possible. Ask your OMRON representative for details.

### M16 -J (Rectangular) Models **Solder Terminal Models**

Appearance	Lighting	Degree of protection	IP40	IP66 oil-resistant type	Display color symbol *
Rectangular (M16-J)		5 VDC	M16-J□-5D	M165-J□-5D	R: red Y: yellow
LED without Volta Reduction Unit	LED without Voltage Reduction Unit	12 VAC/VDC	M16-J□-12D	M165-J□-12D	G: green A: blue W: white
		24 VAC/VDC	M16-J□-24D	M165-J⊡-24D	PY: pure yellow PW: pure white

 $^{\ast}$  Enter the desired color symbol into  $\Box$  in the model number.

#### M16 -A (Square) Models **Solder Terminal Models**

Appearance	Degree of protection Lighting		IP40	IP66 oil-resistant type	Display color symbol *
Square (M16-A)		5 VDC	M16-A□-5D	M165-A□-5D	R: red Y: yellow
LED without Voltage Reduction Unit	LED without Voltage Reduction Unit	12 VAC/VDC	M16-A□-12D	M165-A□-12D	G: green A: blue W: white
		24 VAC/VDC	M16-A□-24D	M165-A□-24D	PY: pure yellow PW: pure white

\* Enter the desired color symbol into  $\Box$  in the model number.

## M16 -T (Round) Models

#### **Solder Terminal Models**

Appearance	Lighting	Degree of protection	IP40	IP66 oil-resistant type	Display color symbol *
Round (M16-T)		5 VDC	M16-T□-5D	M165-T□-5D	R: red Y: yellow
	LED without Voltage Reduction Unit	12 VAC/VDC	M16-T□-12D	M165-T□-12D	G: green A: blue W: white
		24 VAC/VDC	M16-T□-24D	M165-T□-24D	PY: pure yellow PW: pure white


Note: Neon lamps are not available with models that are ordered as a set. They must be ordered individually if required.

\* Enter the desired color symbol into  $\Box$  in the model number.

Individual models: Refer to pages 4 to 6. (The Display, Lamp, Case, and Switch can be ordered separately.) Accessories, replacements, and tools: Refer to the A16.

- Ratings and characteristics: Refer to the A16.
- Dimensions: Refer to pages 8 to 9.

Ordering Individually......Displays, Cases, Lamps, and Sockets can be ordered separately. Combinations that are not available as sets can be created using individual parts. Also, store the parts as spares for maintenance and repairs.



· For colored illumination, order the Display, Case, Lamp, and Socket Unit separately.

#### **Display Set**

Appearance	Class	ification	Model
		Rectangular (2-way guard)	A16-J□M
J.S.	IP40	Square (2-way guard)	A16-A□M
		Round (projecting model)	A16-T□M
		Rectangular (2-way guard)	A165-J⊡M
	IP66 oil-resistant type	Square (2-way guard)	A165-A⊡M
		Round (projecting model)	A165-T□M

Insert one of the following symbols into the box in the model number.

Symbol	Color	Remarks
R	Red	
Y	Yellow	
PY	Pure yellow	LED only
А	Blue	
W	White*	
GY	Green	

\* Use this pushbutton color if the illumination color of the LED is white or pure white.

#### Socket Unit Sets with LEDs

Appearance	Classification	Model
	Solder terminals	M16-1-2

#### Socket Unit Sets with Voltage-reduction Lighting (Solder Terminals)

Appearance	Classification	Model	
	100/110 VAC/VDC	M16-1-T1	

Note: The LED has 24-VAC/VDC circuit built in.

#### Socket Unit Sets with Screw-less Clamp Connectors

Appearance		Classifica	Model	
Display		No voltage-reduction lighting		M16-1-2-S
	Display	Voltage-reduc- tion lighting	100/110 VAC/VDC	M16-1-T1-S
		(See note.)	200/220 VAC/VDC	M16-1-T2-S

Note: 1. The LED built into the 100-V model is 24 VAC/VDC. 2. The LED built into the 200-V model is high-intensity 24 VAC/VDC.

Insert symbols into the boxes with circled numbers. 1

Symbol	Color
R	Red
Y	Yellow
А	Blue
W	White
G	Green

2

Symbol	Туре	Operating voltage
5D	LED	5 VDC
12D		12 VAC/VDC
24D		24 VAC/VDC

Ordering Individually ......Displays, Cases, Lamps, and Sockets can be ordered separately. Combinations that are not available as sets can be created using individual parts. Also, store the parts as spares for maintenance and repairs.

## Display

### For LED-lighted Models

Sealing	IP40			IP66 oil-resistant type		
	Rectangular	Square	Round	Rectangular	Square	Round
Appearance			$\bigcirc$			$\bigcirc$
Color of Display			$\sim$			$\sim$
Red	A16L-JR	A16L-AR	A16L-TR	A165L-JR	A165L-AR	A165L-TR
Yellow	A16L-JY	A16L-AY	A16L-TY	A165L-JY	A165L-AY	A165L-TY
Pure yellow	A16L-JPY	A16L-APY	A16L-TPY	A165L-JPY	A165L-APY	
Green	A16L-JGY	A16L-AGY	A16L-TGY	A165L-JGY	A165L-AGY	A165L-TGY
White	A16L-JW	A16L-AW	A16L-TW	A165L-JW	A165L-AW	A165L-TW
Blue	A16L-JA	A16L-AA	A16L-TA	A165L-JA	A165L-AA	A165L-TA

## Lamp

## LED

Operating voltage	High intensity			
Color	5 VDC	12 VAC/VDC	24 VAC/VDC	
Red	A16-5DSR	A16-12DSR	A16-24DSR	
Yellow	A16-5DSY	A16-12DSY	A16-24DSY	
Green	A16-5DSG	A16-12DSG	A16-24DSG	
White *	A16-5DSW	A16-12DSW	A16-24DSW	
Blue	A16-5DA	A16-12DA	A16-24DA	
Pure white	A16-5DPW	A16-12DPW	A16-24DPW	

\* Use the white LED when the required illumination color is white or pure yellow.

#### Case

Appearance	Classif	Model number	
	IP40	Rectangular	A16-CJM
		Square	A16-CAM
		Round	A16-CTM
	IP66 oil-resistant type	Rectangular	A165-CJM
		Square	A165-CAM
		Round	A165-CTM

#### Socket

Appearance	Class	Model number		
	Solder terminals			M16-0
	PCB t	M16-0P		
Solder terminals	Screw-Less Clamp			M16-S
	Solder terminals	Voltage- reduction lighting	100 V	M16-T1
	Screw-less Clamp		100 V	M16-T1-S
			200 V	M16-T2-S

Ordering set combinations: Refer to page 3.

- Accessories, replacements, and tools: Refer to the A16.
- Ratings and characteristics: Refer to the A16.
- Dimensions: Refer to pages 8 to 9.

## Specifications

## **Approved Standard Ratings**

## UL, cUL (File No. E76675)

LED:

24 VDC max.

Note: Certification has been obtained for the Socket Unit. For detailed information on individual products that have received certification, consult your supplier.

#### Ratings

•	
Ambient operating temperature	-10°C to 55°C (with no icing or condensation)
Ambient operating humidity	35% to 85%RH
Ambient storage temperature	-25°C to 65°C (with no icing or condensation)

### Super-bright LED

Rated voltage	Rated current	Operating voltage	Built-in limiting resistance
5 VDC	8 mA	5 VDC ±5%	Red, yellow, white: $300 \Omega$ Green, blue, pure white: $160 \Omega$
12 VAC/VDC		12 VAC/VDC ±5%	Red, yellow, white: 1 k $\Omega$ Green, blue, pure white: 910 $\Omega$
24 VAC/VDC		24 VAC/VDC ±5%	2.4 kΩ


## **Characteristics**

#### Screw-less Clamp


Item	Туре	Screw-less Clamp			
Recommended wire size		0.5 mm <sup>2</sup> twisted wire or 0.8 mm-dia. solid wire			
Usable wires	Twisted wire	0.3 mm <sup>2</sup>	0.5 mm <sup>2</sup>	0.75 mm <sup>2</sup>	1.25 mm <sup>2</sup>
and tensile	Solid wire	0.5 mm dia.	0.8 mm dia.	1.0 mm dia.	
strength	Tensile strength	10 N	20 N	30 N	40 N
Length of exposed wire		10 ±1 mm			
Compliant sta	ndards	JIS C 2811 Terminal Blocks for Industrial Use		trial Use	


# M16

### Dimensions (Refer to the A16 for details of panel cutout dimensions.)




## Dimensions





#### **Terminal Arrangement**



#### Accessories, Replacements, and Tools

The accessories, replacements, and tools are also used with the A16 Pushbutton Switch. Refer to the A16 datasheet.


### **Safety Precautions**

Refer to Safety Precautions for All Pushbutton Switches/Indicators and Safety Precautions for the A16.

#### Precautions for Correct Use

#### Mounting

• When mounting the Case onto the Socket Unit, ensure that the orientation is correct. Perform mounting with the dimple on the Case and the TOP mark on the Socket Unit facing in the same direction.



#### Wiring

- When using stranded wire, gather the ends of the strands together before wiring.
- When wiring, insert the wire until it comes into contact with something. After wiring is completed, pull on the wires to confirm that they are connected securely.
- After wiring, ensure that continuous pressure is not applied to the terminals.
- Refer to internal connections diagrams and confirm the terminal numbers before performing wiring.

#### Screw-less Clamps

#### **Mounting Procedure**

- 1. Strip a length of 10 mm off the end of the wire (allowable range:  $10\pm1$  mm).
- 2. Bunch wire strands together and straighten them.
- 3. Insert the wire into the insertion hole while pressing the release button at the side of the hole. (Using a precision screwdriver is recommended.)
- 4. Let go of the release button to lock the wire into place.
- 5. After locking, pull on the wire gently to confirm that it is securely locked.

#### **Removing Procedure**

- 1. Remove wires by pulling them while pressing the release button.
- Note: When reusing wires that have already been locked, cut off the end of the wire and strip the wire again before using.

#### Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

**OMRON** Corporation Industrial Automation Company