**Round Water-resistant Connectors (M12 Threads)** 



## Water- and Environment-resistive FA Connectors Save Wiring and Maintenance Effort

- Compact FA connectors meet IP67 requirements and ensure a 94V-0 fire retardant rating.
- A wide array of connectors makes a wiring system more modular, simplifies maintenance, and reduces downtime.
- Connectors with Cables and Connector Assemblies are available.
- Three types of Connector Assembly: Crimping, soldering, and screw-on.
- · Connectors with Cables are UL certified.
- Based on IEC61076-2-101 (IEC60947-5-2) and NECA 4202.

Refer to Safety Precautions on page 32.



## Model Number Legend

#### **Connectors with Cables Model Number Legend**

Connector	Cable specifications	XS	2: M12 Screw Connecti	XS5: One-touch Smartclick Connection * (compatible with M12 connectors)		
		Cable length (m)	Model	Reference page	Cable length (m)	Model
		0.5	XS2W-D421-B81-F		0.5	XS5W-D421-B81-F
		1	XS2W-D421-C81-F		1	XS5W-D421-C81-F
		2	XS2W-D421-D81-F		2	XS5W-D421-D81-F
		3	XS2W-D421-E81-F		3	XS5W-D421-E81-F
	Fire-retardant, PVC robot cable	4	XS2W-D421-F81-F		4	XS5W-D421-F81-F
Connectors on both cable ends	Cable	5	XS2W-D421-G81-F	4	5	XS5W-D421-G81-F
cable enus		10	XS2W-D421-J81-F		10	XS5W-D421-J81-F
		15	XS2W-D421-K81-F		15	XS5W-D421-K81-F
		20	XS2W-D421-L81-F		20	XS5W-D421-L81-F
	Constant registerat apple	2	XS2W-D421-D81-SA		2	XS5W-D421-D81-SA
	Spatter-resistant cable	5	XS2W-D421-G81-SA		5	XS5W-D421-G81-SA
	Fire-retardant, PVC robot cable	1	XS2F-D421-C80-F		1	XS5F-D421-C80-F
		2	XS2F-D421-D80-F		2	XS5F-D421-D80-F
		3	XS2F-D421-E80-F		3	XS5F-D421-E80-F
Connector on one cable		5	XS2F-D421-G80-F		5	XS5F-D421-G80-F
end		10	XS2F-D421-J80-F	6	10	XS5F-D421-J80-F
(Socket)		15	XS2F-D421-K80-F		15	XS5F-D421-K80-F
		20	XS2F-D421-L80-F		20	XS5F-D421-L80-F
	Constant registerat apple	2	XS2F-D421-D80-SA		2	XS5F-D421-D80-SA
	Spatter-resistant cable	5	XS2F-D421-G80-SA		5	XS5F-D421-G80-SA
		0.3	XS2H-D421-A80-F		0.3	XS5H-D421-A80-F
		0.5	XS2H-D421-B80-F		0.5	XS5H-D421-B80-F
	Fire-retardant, PVC robot	1	XS2H-D421-C80-F	1	1	XS5H-D421-C80-F
Connector on one cable end	cable	2	XS2H-D421-D80-F	13	2	XS5H-D421-D80-F
(Plug)		3	—	13	3	XS5H-D421-E80-F
x - 3/		5	XS2H-D421-G80-F	1	5	XS5H-D421-G80-F
	Spotter registent apple	0.3	XS2H-D421-A80-SA	1	0.3	XS5H-D421-A80-SA
	Spatter-resistant cable	1	XS2H-D421-C80-SA	1	1	XS5H-D421-C80-SA

\*For details, refer to the data sheet of the XS5 Round Water-resistant Connectors (M12 Smartclick).

Note 1. Only DC, straight, 4-core types, and common cable specifications are shown above. Refer to the relevant pages for other products.

2. Other than the M12 sizes introduced above, M8-sized (XS3) products are also available.

For details, refer to the data sheet of the XS3 Round Water-resistant Connectors (M8/S8).

#### XS2: M12 Screw Connection

### XS5: One-touch Smartclick Connection\* (compatible with M12 screws)

Note: Screw connections will be made if connecting with a screw type.



Turn approx. 1/8 of a turn to connect Connections can be checked using markings

\*For details, refer to the data sheet of the XS5 Round Water-resistant Connectors (M12 Smartclick).

## **Ratings and Specifications**

Rated current	4 A
Rated voltage	250 VAC/VDC
Contact resistance (Connector)	40 mΩ max. (20 m V max. and 100 mA max.)
Insulation resistance	1,000 MΩ min. (at 500 VDC)
Dielectric strength (Connector)	1,500 VAC for 1 min (leakage current: 1 mA max.)
Degree of protection	IP67 (IEC60529)
Insertion tolerance	200 times
Cable holding strength	Cable diameter: 6 mm         98 N/15 s           4 to 5 mm         49 N/15 s           3 mm         29 N/15 s
Ambient operating temperature range	-25 to 70°C *
Ambient humidity range	20% to 85%

\*Use the PVC robot cable within a temperature range between 0°C and 70°C to prevent the wires inside the cable from being broken when bending it.

#### **Materials and Finish**

Item	Model	XS2F/H/W	XS2F-LED	XS2M/R/P	XS2C/G
Contacts		Copper alloy/Gold plating		Brass	
Thread b	racket	Brass/Copper alloy *		ł	
Pin block	(	PBT resin		PA resin	PBT resin
O-ring		Rubber			+
Cover		Soft PBT resin	TPU resin	—	PBT resin
	Fire-retardant, PVC robot cable	UL AWM2464 CL3, 6 mm dia. AWG20	—	—	—
	Non-polar DC Connectors with Standard PVC cable	6 mm dia. AWG20	—	—	—
	E2E models with conventional connector pin with Fire- retardant, PVC robot cable	UL AWM2464 CL3, 6 mm dia. AWG20	_	_	_
Cable	Standard PVC cable up to 105°C	6 mm dia. AWG20	_	_	_
	Spatter-resistant cable	6.6 mm dia. AWG20	—	—	_
	Standard PVC cable (XS2F-LED)	_	UL AWM2464 5.0 mm dia. (3 conductors) 5.4 mm dia. (4 conductors) 0.34 mm <sup>2</sup>	_	_

\*The T-joint of the XS2R is aluminum/white.

## Pin Arrangement (Engaged Side)

Item	Item No. of poles		5 poles	
DC type	Male (plug) contacts			
	Female (socket) contacts			
AC type	Male (plug) contacts			
, o tipe	Female (socket) contacts			

Note: The AC and DC mating section forms are different as shown here and therefore cannot be connected together.

## **Connections**

## **Connection Combinations**

OMRON model No.		M12 Plug Connectors XS2H, XS2G, XS2W (plug side), XS2R (plug side), XS2M	Smartclick Plug Connectors XS5H, XS5G, XS5W (plug side), XS5R (plug side), XS5M	
M12 Socket Connectors	XS2F, XS2C, XS2W (socket side), XS2R (socket side), XS2P	0	0	
Smartclick Socket Connectors	XS5F, XS5C, XS5W (socket side), XS5R (socket side), XS5P	О	۵	

Onnected by twisting.


O: Connected by screwing. Note: The XS M and XS P cannot mate with each other.

## XS2W Sockets and Plugs on Both Cable Ends

## **Model Number Structure**

## **Model Number Legend**

Use this model number legend to identify products from their model number. Use this model number legend to identify products from their model number. When ordering, use a model number from the table in *Ordering Information*.



## 1. Type

W: Connectors with cables, socket and plug on both cable ends

## 2. AC/DC (Mating Section Form)

D: For DC

## 3. Connector Poles

- 4: 4 poles
- 5: 5 poles

## 4. Contact Plating

2: Gold plating

## 5. Cable Connection Direction

- 1: Straight (socket)/Straight (plug)
- 2: Right-angle (socket)/Right-angle (plug)
- 3: Straight (socket)/Right-angle (plug)
- 4: Right-angle (socket)/Straight (plug)

### 6. Cable Length

- A : 0.3 m
- B : 0.5 m
- C:1m
- D:2m
- E:3m
- F:4m
- G:5m
- H:7m J:10m
- K : 15 m
- L : 20 m

## 7. Connections (Numbers inside circles are terminal numbers)

- 8 : (1) Brown, (2) White, (3) Blue, (4) Black (for DC)
- G: 1 Brown, 2 White, 3 Blue, 4 Black, 5 Gray

## 8. Connectors on One End/Both Ends

1: Both ends

## 9. Cable Specifications

- F : Fire-retardant, PVC robot cable
- SA : Spatter-resistant cable

XS2

## XS2W Sockets and Plugs on Both Cable Ends

## **Ordering Information**


Cable specifications	Cable connection direction	Cable diameter (mm)	No. of cable cores	Cable core cross-sectional area (mm <sup>2</sup> )	Cable length L (m)	DC Model	UL
		()	00100	ulou (iiiii )	0.5	XS2W-D421-B81-F	
					1	XS2W-D421-C81-F	-
					2	XS2W-D421-D81-F	-
					3	XS2W-D421-E81-F	
	Straight (Plug)/ Straight (Socket)				4	XS2W-D421-F81-F	-
		6.0 dia.	4	0.5	5	XS2W-D421-G81-F	UL 2238 certified (File No. E207683)
					10	XS2W-D421-J81-F	
Fire retardent DVC					15	XS2W-D421-K81-F	
Fire-retardant, PVC robot cable					20	XS2W-D421-L81-F	
	Right-angle (Plug)/				2	XS2W-D422-D81-F	
	Right-angle (Socket)				5	XS2W-D422-G81-F	
	Straight (Socket)/				2	XS2W-D423-D81-F	
	Right-angle (Plug)				5	XS2W-D423-G81-F	
					1	XS2W-D424-C81-F	
	Right-angle (Socket)/ Straight (Plug)				2	XS2W-D424-D81-F	
					5	XS2W-D424-G81-F	
					10	XS2W-D424-J81-F	
Spatter-resistant cable	Straight (Plug)/	6.6 dia.			2	XS2W-D421-D81-SA	
Spatter-resistant cable	Straight (Socket)	0.0 ula.			5	XS2W-D421-G81-SA	

Note: Ask your OMRON representative about other cable lengths, and about 5-core cables.


XS2

## Dimensions


Straight (Socket)/Straight (Plug) Fire-retardant, PVC robot cable XS2W-D421- $\Box$ 81-F Spatter-resistant cable XS2W-D421-D81-SA




## Right-angle/Right-angle Fire-retardant, PVC robot cable XS2W-D422-\_81-F




Wiring Diagram for 4 Cores




#### Straight (Socket)/Right-angle (Plug) Fire-retardant, PVC robot cable XS2W-D423281-F



#### Wiring Diagram for 5 Cores



#### Right-angle (Socket)/Straight (Plug) Fire-retardant, PVC robot cable XS2W-D421 81-F




## XS2F Socket on One Cable End

## **Model Number Structure**

## **Model Number Legend**

Use this model number legend to identify products from their model number. Use this model number legend to identify products from their model number. When ordering, use a model number from the table in *Ordering Information*.



### 1. Type

F: Connector with cables, socket on one cable end

#### 2. AC/DC (Mating Section Form)

- A: For AC
- D: For DC

E: For DC, stainless steel lock

#### 3. Connector Poles

- 4: 4 poles
- 5: 5 poles

### 4. Contact Plating

2: Gold plating

#### 5. Cable Connection Direction

- 1: Straight
- 2: Right-angle

#### 6. Cable Length

- A : 0.3 m
- B : 0.5 m
- C :1 m
- D:2m
- E :3 m
- F:4m
- G:5m
- H : 7 m
- J : 10 m
- K : 15 m
- L : 20 m

Note: Only the 2 m (D), 5 m (G) and 10 m (J) cables are available for cables with 5 poles.

## 7. Connections

### (Numbers inside circles are terminal numbers)

A : ① Brown, ②,	<b>③</b> ,	Blue (for DC)
В: ①, ②,	<li>3 Brown,</li>	Blue (for AC)
C : ① Brown, ②,	<li>3 Blue,</li>	④ Black
D: ①, ②,	<li>3 Blue,</li>	④ Brown
0 · ( Drown ( White	() Plue	Reack (for DC)

- 8 : (1) Brown, (2) White, (3) Blue, (4) Black (for DC)
- 9 : 1 Brown, 2 White, 3 Blue, 4 Black (for AC)
- G : 1) Brown, 2 ---, 3) Blue, 4) Black, 5) Gray

## 8. Connectors on One End/Both Ends

0: One end

### 9. Cable Specifications

- F: Fire-retardant, PVC robot cable
- E: Heat-resistant cable up to 105°C
- SA: Spatter-resistant cable
- A: Standard PVC cable

Note: E type and SA type is a 4-core cable.

### \_\_\_\_\_

Designations for Non-polar DC (For Limit Switches and Sensors)

### 6. Cable Length

- 3:2 m 4:5 m
- 7. Connections (Numbers inside circles are terminal numbers)
  - 1: (1) ---, (2) ---, (3) Black, (4) White
- 8. Connectors on One End/Both Ends 0: One end
- 9. Cable Specifications

Not designated.

Note: DC non-polarity models have different specific codes. (6, 7 and 9)

## XS2F Socket on One Cable End


## **Ordering Information**

Cable	Cable	No. of	Cable	Cable core cross-	Cable	DC	AC																									
specifications	connection direction	cable cores	diameter (mm)	sectional area (mm <sup>2</sup> )	length L (m)	Model	Model	UL																								
		2				XS2F-D421-CA0-F	XS2F-A421-CB0-F																									
		3				XS2F-D421-CC0-F	_																									
		4				XS2F-D421-C80-F	XS2F-A421-C90-F																									
		2				XS2F-D421-DA0-F	XS2F-A421-DB0-F																									
		3			2	XS2F-D421-DC0-F	_																									
		4				XS2F-D421-D80-F	XS2F-A421-D90-F																									
		4			3	XS2F-D421-E80-F	_																									
	Straight	2				XS2F-D421-GA0-F	XS2F-A421-GB0-F																									
		3			5	XS2F-D421-GC0-F	_																									
		4				XS2F-D421-G80-F	XS2F-A421-G90-F																									
		2				XS2F-D421-JA0-F	XS2F-A421-JB0-F																									
		3			10	XS2F-D421-JC0-F	_																									
						XS2F-D421-J80-F	XS2F-A421-J90-F	UL 2238																								
-ire-retardant,		4			15	XS2F-D421-K80-F	_	certified																								
VC robot cable					20	XS2F-D421-L80-F	_	(File No.																								
		2	-			XS2F-D422-CA0-F	XS2F-A422-CB0-F	E207683)																								
		3			1	XS2F-D422-CC0-F	_																									
		4				XS2F-D422-C80-F	_																									
		2		-		XS2F-D422-DA0-F	XS2F-A422-DB0-F																									
		3			2	XS2F-D422-DC0-F	_																									
		4	6.0 dia.			XS2F-D422-D80-F	_																									
	Right-angle	4	-	0.5	3	XS2F-D422-E80-F	_																									
	r light angle	2	-			XS2F-D422-GA0-F	XS2F-A422-GB0-F																									
		3		5	XS2F-D422-GC0-F	_																										
		4						_	XS2F-D422-G80-F																							
					-	-	-	-							ł		÷	ł		-			-							XS2F-D422-JA0-F	XS2F-A422-JB0-F	
														10	XS2F-D422-JC0-F	_																
		4				XS2F-D422-J80-F																										
Non-polar DC		2			2	XS2F-D421-310	XS2F-A421-310																									
Connectors with	Straight	2	+		5	XS2F-D421-410	XS2F-A421-410																									
Standard PVC		2			2	XS2F-D422-310	XS2F-A422-310	—																								
cable	Right-angle	2	-		5	XS2F-D422-410	XS2F-A422-410																									
E2E models with		2	-		2	XS2F-D421-DD0	_																									
conventional	Straight	2	+		5	XS2F-D421-GD0																										
connector pin with		2			2	XS2F-D422-DD0		—																								
Fire-retardant, PVC robot cable	tardant, Right-angle	5	XS2F-D422-GD0	_																												
Heat-resistant	Straight				2	XS2F-E421-D80-E	—																									
cable up to		4			5	XS2F-E421-G80-E	—	_																								
	Right-angle				2	XS2F-E422-D80-E	—																									
					5	XS2F-E422-G80-E	—																									
Spatter-	Straight	4	6.6 dia.		2	XS2F-D421-D80-SA	—																									
resistant cable	Stagn	- T	0.0 ula.		5	XS2F-D421-G80-SA																										
					2	XS2F-D521-DG0-A	_																									
Standard PVC	Straight				5	XS2F-D521-GG0-A																										
able		5	6.0 dia.	0.3	10	XS2F-D521-JG0-A		—																								
	Dight angle				2	XS2F-D522-DG0-A	—																									
	Right-angle				5	XS2F-D522-GG0-A																										


Note: Ask your OMRON representative about other cable lengths. \*The heat-resistant fixture material is SUS316L stainless steel without surface treatment.

## Dimensions

Straight Connectors Fire-retardant, PVC robot cable XS2F-D421-\_\_\_\_O-F XS2F-A421-\_\_\_O-F Non-polar DC Connectors with Standard PVC cable XS2F-D421-\_\_\_O XS2F-A421-\_\_\_O E2E models with conventional connector pin with Fire-retardant, PVC robot cable XS2F-D421-\_\_\_O Heat-resistant cable up to 105°C XS2F-E421-\_\_B0-E Spatter-resistant cable XS2F-D421-\_\_B0-SA



Right-angle Connectors Fire-retardant, PVC robot cable XS2F-D422-\_\_\_\_O-F XS2F-A422-\_\_\_O-F Non-polar DC Connectors with Standard PVC cable XS2F-D422-\_\_\_O XS2F-A422-\_\_\_O E2E models with conventional connector pin with Fire-retardant, PVC robot cable XS2F-D422-\_\_\_O Heat-resistant cable up to 105°C XS2F-E422-\_\_\_80-E




### Wiring Diagram

		Two-core	Three-core	Four-core
Fire-retardant, PVC robot cable	XS2F-0420-00-F	Contact No. Cable lead Colors Brown		
Spatter-resistant cable *	XS2F-D421-□80-SA	Brown Blue (DC)	Contact No. Cable lead colors	Contact No. Cable lead olors White Blue Blue Black
Heat-resistant cable up to 105°C *	XS2F-E42□-□80-E	Contract NO. Cable read	Black (DC)	0 Black (DC/AC)
Non-polar DC Connectors with Standard PVC cable	XS2F420	Contact No. Cable lead colors Black	_	_
E2E models with conventional connector pin with Fire-retardant, PVC robot cable	XS2F-D42□-□D0	Contact No. Cable lead colors	_	_

\*Spatter-resistant Cables and Heat-resistant Cables (105°C) are available only for four cores and DC.

#### (Unit: mm)






For details on connecting with E2E Proximity Sensors, refer to E2E Small-diameter Proximity Sensor Data Sheet (Cat. No.: SCEC-044).

## **XS2F-G/H** Connectors with Cables, Socket on One Cable End, Screw Loosening-preventing Structure Type

## **Model Number Structure**

## **Model Number Legend**

Use this model number legend to identify products from their model number. Use this model number legend to identify products from their model number. When ordering, use a model number from the table in *Ordering Information*.



1. Type

F: Connector with cables, sockets on one cable end

## 2. AC/DC

- G: For DC
- H: For AC

## 3. Cable Connection Direction

- 1: Straight
- 2: Right-angle

## 4. Cable Length

G80 : 5m (for DC) G90 : 5m (for AC) J80 : 10m (for DC) J90 : 10m (for AC)

## 5. Structure


Screw Loosening-preventing

## **Ordering Information**

Cable connection	No. of cable cores	Cable length L (m)	DC	AC	UL
direction	NO. OI CADIE COIES		Model	Model	
Straight		5	XS2F-G421-G80-F	XS2F-H421-G90-F	
Straight	4	10	XS2F-G421-J80-F	XS2F-H421-J90-F	UL 2238 certified
Pight angle	4	5	XS2F-G422-G80-F	XS2F-H422-G90-F	(File No. E207683)
Right-angle		10	XS2F-G422-J80-F	XS2F-H422-J90-F	

XS2

## Dimensions



## Features

## Screw Loosening-preventing Structure Appearance



### Structure



By the above structure, the convex and concave portion of the thread bracket and housing ribs interfere with each other at  $45^{\circ}$  increments to work as a loosening-preventing mechanism when engaged.

# XS2F Sockets on One Cable End with Indicator

## **Model Number Structure**

## **Model Number Legend**

Use this model number legend to identify products from their model number. Use this model number legend to identify products from their model number. When ordering, use a model number from the table in Ordering Information.

#### XS2F-M12PVC Δ 1 5 3 4 6

### 1. Type

F: Connector with cables, sockets on one cable end

2

## 4. Connector Poles

- 3: 3 poles 4: 4 poles
- 2. Mating Section Form M12: M12
- **5. Cable Connection Direction** A: Right-angle
- 7. Applicable Sensors
  - P: PNP
  - N: NPN
- 8. With indicator LED: With indicator

- 3. Cable Material
  - PVC: PVC

## 6. Cable Length

2 :2 m 5 :5 m 10:10 m


## **Ordering Information**

Cable specifications	Cable connection direction	Cable diameter (mm)	No. of cable cores	Cable core cross- sectional area (mm <sup>2</sup> )	Cable length L (m)	LED	Model	UL			
					2		XS2F-M12PVC3A2MPLED				
									5 PNP	XS2F-M12PVC3A5MPLED	
		5 dia.	3		10	0	XS2F-M12PVC3A10MPLED				
			3		2		XS2F-M12PVC3A2MNLED	UL 2238			
PVC	<b>Right-angle</b>		5	NPN	XS2F-M12PVC3A5MNLED	certified (File No.					
					10		XS2F-M12PVC3A10MNLED	E207683)			
					2			XS2F-M12PVC4A2MPLED			
		5.4 dia.	4		5	PNP	XS2F-M12PVC4A5MPLED				
					10		XS2F-M12PVC4A10MPLED				

## Dimensions

**Right-angle** XS2F-M12PVC3A MPLED XS2F-M12PVC4A MPLED





## Wiring Diagram

3 р	4 poles		
NPN	PNP	PNP	
1 oo+ BROWN	1 o	1 0	
¥∄YELLOW ¥∄ GREEN	4 0	4 0 BLACK	
4 oo black	↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓	R1[] R2[] R3[] D1≢3 D2≢3 D3≢3	
3 0	3 0 0 - BLUE	3 0 BLUE	


(Unit: mm)

## XS2H Plugs on One Cable End

## **Model Number Structure**

## **Model Number Legend**

Use this model number legend to identify products from their model number. When ordering, use a model number from the table in *Ordering Information*.



## 1. Type

H: Connector with cables, plug on one cable end

## 2. AC/DC

- A: For AC
- D: For DC

## 3. Connector Poles

- 4: 4 poles
- 5: 5 poles

## 4. Contact Plating

2: Gold plating

## **5. Cable Connection Direction**

1: Straight

## 6. Cable Length

- A : 0.3 m
- B : 0.5 m
- C : 1 m
- D:2m
- G : 5 m

## 7. Connections (Numbers inside circles are terminal numbers)

8 : 1 Brown, 2 White, 3 Blue, ④ Black (for DC) 9 : (1) Brown, (2) White, (3) Blue, (4) Black (for AC) A : 1 Brown, 2 ---, **(3)** ----, (4) Blue (for DC) **2**---, В:①---, (3) Brown, (4) Blue (for AC) (4) Black (for DC) C : (1) Brown, (2) ---, 3 Blue, G: (1) Brown, (2) White, (3) Blue, 4 Black, (5) Gray

## 8. Connectors on One End/Both Ends

0: One end

## 9. Cable Specifications

- A :Standard cable
- F :Fire-retardant, PVC robot cable
- SA :Spatter-resistant cable

## XS2H Plugs on One Cable End

## **Ordering Information**

Cable specifications	No. of connector poles	Cable connection direction	Cable diameter (mm)	No. of cable cores	Cable core cross- sectional	Cable length L (m)	DC Model	AC Model	UL
	P		()		area (mm²)	- ()	XS2H-D421-AA0-F		
				2				XS2H-A421-AB0-F	_
				3		0.3	XS2H-D421-AC0-F	—	
<b>-</b>	4	t Straight Connectors	6.0 dia.	4			XS2H-D421-A80-F	XS2H-A421-A90-F	
					0.5	0.5	XS2H-D421-B80-F	—	<ul> <li>UL 2238</li> <li>certified</li> <li>(File No.</li> <li>E207683)</li> </ul>
Fire-retardant, PVC robot cable				2		1	XS2H-D421-CA0-F	XS2H-A421-CB0-F	
F VC TODOL CADIE				3			XS2H-D421-CC0-F	_	
				4			XS2H-D421-C80-F	XS2H-A421-C90-F	L207000)
						2	XS2H-D421-D80-F	_	
						5	XS2H-D421-G80-F	_	
Spatter-	4	-	6 6 dia	4		0.3	XS2H-D421-A80-SA	_	
resistant cable	4		6.6 dia.	4		1	XS2H-D421-C80-SA	_	1
Standard	5	1	6.0 dia.	5	0.3	0.3	XS2H-D521-AG0-A	_	1 —
cable	э	S	0.0 Ula.	5	0.3	1	XS2H-D521-CG0-A	_	1

Note: Ask your OMRON representative about other cable lengths.


## **Dimensions**

## Straight (4 poles)


Fire-retardant, PVC robot cable XS2H-421-00-F Spatter-resistant cable XS2H-D421-D80-SA

5 dia







Wiring Diagram



Three-cores






50


Four-cores

Straight (5 poles)

Standard cable XS2H-D521G0-A (For DC)



### Wiring Diagram



(Unit: mm)

# XS2 Sensor I/O Connectors on Cables (8-pole)

## **Ordering Information**

Connector type	Cable connection direction	Number of cores	Cable length L (m)	Applicable wire diameter	Model	UL
Panel-mounting Plug					XS2M-D824-4	—
Developmenting an elect	1 —	—	_	AWG22 to 28	XS2P-D821-2	
Panel-mounting socket					XS2P-D822-2	
Divergence coble and			0.3		XS2H-D821-AH0-C	UL 2238
Plug on one cable end			1	- - - -	XS2H-D821-CH0-C	certified
Cooket on one coble and	Otroight	0	2		XS2F-D821-DH0-C	(File No.
Socket on one cable end	Straight	8	5		XS2F-D821-GH0-C	E207683)
Diver and applying an both pable and	1		2	1	XS2W-D821-DH1-C	1
Plug and socket on both cable ends			5	1	XS2W-D821-GH1-C	1

Note: Ask your OMRON representative about other cable lengths. Ask your OMRON representative about PVC robot cable models (-R).

## **Ratings and Specifications**

Rated current	1.5 A
Rated voltage	36 VDC
Contact resistance	40 mΩ max. (at 20 mVDC max. and 100 mA max.)
Insulation resistance	1,000 MΩ min. (at 500 VDC)
Dielectric strength	1,000 VAC for 1 min (leakage current: 1 mA max.)
Degree of protection	IP67
Insertion tolerance	200 times min.
Ambient operating temperature range	-25 to 70°C

## **Materials and Finish**

Contacts		Brass, gold plating
Thread Bracket, body, M16 nuts		Brass/nickel plated
Pin block		PBT resin, light gray
Cover *1		Soft PBT resin
Seal rubb	er and O-ring *2	Rubber
Cable	Standard cable	6 mm dia.
Cable	(8 core, shielded)	AWG24


\*1. XS2F/XS2H/XS2W only. \*2. O-rings are on sockets only.

### **Pins and Cable Lead Colors**

		Pin No.							
XS2F/XS2H/XS2W cable lead	1	2	3	4	5	6	7	8	
colors	White	Brown	Green	Yellow	Gray	Pink	Blue	Shield	

## Wiring


### Wiring Example



## Dimensions


Plug on One Cable End (M12) XS2H







## Socket on One Cable End (M12) XS2F





Socket and Plug on Both Cable Ends (M12) XS2W





## XS2G Crimping/Soldering Plug Assemblies

## **Ordering Information**


Suitable cable	Core conductor	Suitable sheath	Cable	Connection	DC	AC		
(mm)	size (mm <sup>2</sup> )	material connection		method	Model	Model	UL	
6 dia. (5 to 6 dia.)	0.18 to 0.3 0.5 to 0.75*		Straight	Crimping	XS2G-D4C1	XS2G-A4C1		
	0.5 max.			Soldering	XS2G-D421	XS2G-A421		
	0.5 max.		Right-angle	Soldening	XS2G-D422	—		
Adia (Ata Edia)	0.18 to 0.3 0.5 to 0.75*		Straight	Crimping	XS2G-D4C3	XS2G-A4C3	UL 2238 certified	
4 dia. (4 to 5 dia.)	0.5 max.	PVC, PE, PUR	_	Soldering	XS2G-D423	XS2G-A423	(File No.	
	0.5 max.		Right-angle	Soldening	XS2G-D424	—	E207683)	
3 dia. (3 to 4 dia.)	0.18 to 0.3 0.5 to 0.75*	1	Straight	Crimping	XS2G-D4C5	XS2G-A4C5		
	0.5 max.			Soldering	XS2G-D425	XS2G-A425	-	
	0.5 max.		Right-angle	Soldening	XS2G-D426	—		

\*There are two types of contacts.

Note: Crimping plug pins are sold separately.

Use a cable of mentioning. If you do not use one of these cables, there is a possibility that the performance can't be met.

## Dimensions



## XS2U Crimping Pin for XS2G


## **Ordering Information**

Suitable core size (mm <sup>2</sup> )	Model
0.18 to 0.3	XS2U-3121
0.5 to 0.75	XS2U-3122

## **Dimensions**

XS2U-312

\* A special tool must be used for crimping. For details, refer to page 31.



(Unit: mm)

## XS2C Crimping/Soldering Socket Assemblies


## **Ordering Information**

Suitable cable	Core conductor	Suitable sheath	Cable	Connection	DC	AC		
(mm)	size (mm²)	material connection direction		method	Model Model		UL	
	0.18 to 0.3			Crimping	XS2C-D4C1	XS2C-A4C1		
	0.5 to 0.75*		Straight	Omping	7950-0401	X320-A401		
6 dia. (5 to 6 dia.)	0.5 max.			Soldering	XS2C-D421	XS2C-A421		
0 ula. (5 to 0 ula.)	0.18 to 0.3			Crimping	XS2C-D4C2	XS2C-A4C2		
	0.5 to 0.75*		Right-angle	Chimping	X320-D402	X320-A402		
	0.5 max.			Soldering	XS2C-D422	XS2C-A422		
	0.18 to 0.3		Straight	Crimping	XS2C-D4C3	XS2C-A4C3		
	0.5 to 0.75*			Omping	X320-D403	X320-A403	UL 2238	
4 dia. (4 to 5 dia.)	0.5 max.	- PVC, PE, PUR		Soldering	XS2C-D423	XS2C-A423	certified	
4 ula. (4 to 5 ula.)	0.18 to 0.3		Right-angle	Crimping	XS2C-D4C4	XS2C-A4C4	(File No.	
	0.5 to 0.75*			Chimping	X320-D404	X320-A404	E207683)	
	0.5 max.			Soldering	XS2C-D424	XS2C-A424	1	
	0.18 to 0.3			Crimping	XS2C-D4C5	XS2C-A4C5		
	0.5 to 0.75*		Straight	Omping	7950-0403	X320-A403		
3 dia. (3 to 4 dia.)	0.5 max.	1		Soldering	XS2C-D425	XS2C-A425	1	
	0.18 to 0.3	1		Crimping	XS2C-D4C6	XS2C-A4C6	1	
	0.5 to 0.75*		Right-angle	Chilliping	7920-0400	A320-A400		
	0.5 max.	1		Soldering	XS2C-D426	XS2C-A426	1	

\*There are two types of contacts.

Note: Crimping plug contacts are sold separately. Use a cable of mentioning. If you do not use one of these cables, there is a possibility that the performance can't be met.

## Dimensions



## XS2U Crimping Pin for XS2C


## **Ordering Information**

Suitable core size (mm <sup>2</sup> )	Model
0.18 to 0.3	XS2U-2221
0.5 to 0.75	XS2U-2222

## **Dimensions**

(Unit: mm)

(Unit: mm)



## XS2G Screw-on Plug Assemblies


## **Ordering Information**

No. of poles	Suitable cable (mm)	Core conductor size (mm <sup>2</sup> )	Suitable sheath material	Straight connectors (for DC) Model	Right-angle connectors (for DC) Model	UL
	8 dia. (7 to 8 dia.)			XS2G-D5S7	—	
5	7 dia. (6 to 7 dia.)			XS2G-D5S9	—	
	6 dia. (5 to 6 dia.)			XS2G-D5S1	XS2G-D5S2	
	8 dia. (7 to 8 dia.)	0.18 to 0.75	PVC, PE, PUR	XS2G-D4S7	—	UL 2238 certified
	7 dia. (6 to 7 dia.)	0.10100.75	FVC, FE, FUN	XS2G-D4S9	_	(File No. E207683)
4	6 dia. (5 to 6 dia.)	1		XS2G-D4S1	XS2G-D4S2	
	4 dia. (4 to 5 dia.)	1		XS2G-D4S3	XS2G-D4S4	
	3 dia. (3 to 4 dia.)	1		XS2G-D4S5	XS2G-D4S6	

Note: XS2G Screw-on Plugs cannot be connected to side by side to the CN1 and CN2 connectors of XS2R Y-Joint Sockets/Plugs. Use a cable of mentioning. If you do not use one of these cables, there is a possibility that the performance can't be met.

## Dimensions

(Unit: mm)





39.6

14 dia.

(Unit: mm)

## XS2C Screw-on Socket Assemblies


## **Ordering Information**

No. of poles	Suitable cable (mm)	Core conductor size (mm <sup>2</sup> )	Suitable sheath material	Straight connectors (for DC) Model	Right-angle connectors (for DC) Model	UL
	8 dia. (7 to 8 dia.)		-	XS2C-D5S7	—	
5	7 dia. (6 to 7 dia.)			XS2C-D5S9	—	
	6 dia. (5 to 6 dia.)			XS2C-D5S1	XS2C-D5S2	
	8 dia. (7 to 8 dia.)	0.18 to 0.75	PVC, PE, PUR	XS2C-D4S7	—	UL 2238 certified (File No. E207683)
	7 dia. (6 to 7 dia.)	0.16100.75	FVC, FE, FUR	XS2C-D4S9	—	(File NO. E207003)
4	6 dia. (5 to 6 dia.)	-		XS2C-D4S1	XS2C-D4S2	
	4 dia. (4 to 5 dia.)			XS2C-D4S3	XS2C-D4S4	-
	3 dia. (3 to 4 dia.)			XS2C-D4S5	XS2C-D4S6	

Note: Use a cable of mentioning. If you do not use one of these cables, there is a possibility that the performance can't be met.

## Dimensions

Straight Connectors Applicable Cable Outer Diameter: 8 mm XS2C-D5S7 (5 poles) XS2C-D4S7 (4 poles) Applicable Cable Outer Diameter: 7 mm XS2C-D5S9 (5 poles) XS2C-D4S9 (4 poles)



Straight Connectors Applicable Cable Outer Diameter: 6 mm XS2C-D5S1 (5 poles) XS2C-D4S1 (4 poles) Applicable Cable Outer Diameter: 4 mm XS2C-D4S3 (4 poles) Applicable Cable Outer Diameter: 3 mm XS2C-D4S5 (4 poles) M12×1 20 dia. 14.9 dia.

Right-angle Connectors Applicable Cable Outer Diameter: 6 mm XS2C-D5S2 (5 poles) XS2C-D4S2 (4 poles) Applicable Cable Outer Diameter: 4 mm XS2C-D4S4 (4 poles) Applicable Cable Outer Diameter: 3 mm XS2C-D4S6 (4 poles) 39.6

14 dia

### Assembly Procedure for XS2C/XS2G Connector Assemblies


#### (1) Connector and Cable Diameters

- Connectors for 8, 7, 6, 4, and 3 mm diameter Cables (i.e., Cables that are 7 to 8, 6 to 7, 5 to 6, 4 to 5, and 3 to 4 mm in diameter respectively) are available. When assembling a Connector used with a cable, make sure that the external diameter of the Connector is suited to that of the cable.
- A waterproof bushing for 6/7 mm diameter Cable has no stripe, that for 8/4 mm diameter Cable has a single stripe, and that for 3 mm diameter Cable has two stripes.


#### (2) Component Insertion

#### **Crimping/Soldering Connectors**

#### Straight Connectors



#### **Right-angle Connectors**




\*A ring is not required for Screw-on Connectors.

• As shown in the above illustration, connect the above components to the Cable with its end processed.

#### Screw-on Connectors

#### Confirm that you have all of the required parts.




## Insulation caps and insulation tubes are included with 5-pole Connectors (XS2C-D5S and XS2G-D5S ).

\*1. Rings are not required with 7-mm and 8-mm cables.

\*2. Insert the waterproof bushing for 7-mm and 8-mm cables in the direction shown in the diagram.

### (3) Wiring (Dressing the Cable Ends)


#### Soldering Connectors



- Strip 10 mm of the Cable sheath and 4 mm of each core.
- Before soldering cores and solder cup pins together, soldercoat each of them.
- The following conditions are recommended for soldering each solder cup pin.
  - Soldering temperature: 350±5°C
  - Soldering period: 3±1 s
- The length marked \*A should be 6.5 mm max., otherwise the proper degree of protection of the connector will not be maintained.

#### **Crimping Connectors**


#### Crimping



- Strip 14 mm of the Cable sheath and 4 mm of each core.
- Make sure that each core is not damaged and its end strands are not spread out.
- Mount the XY2F-0003 Locator to XY2F-0002 Crimp Tool, both of which are sold separately, and set the selector dial of the Crimp Tool to 8.
- After mounting the crimping pins to the Locator, fully insert the cores to the crimping pins.
- Squeeze the handle of the Crimp Tool to press-fit the cores to the crimping pins.


(Squeeze the handle firmly until the handle automatically returns to the release position.)

#### Wiring



• After press-fitting the cores to the pins, insert the pins into the pin clamp as shown in the illustration. Then make sure that the lead colors correspond to the pin clamp numbers that are identical to the connector pin numbers.


#### Insertion




• Tentatively insert the pins to the pin block holes so that the key on the pin block will coincide with the key groove on the pin clamp. Then insert the cable along with the pin clamp.

#### Screw-on Connectors


- Dressing the Cable End
- Four-pole Connectors




• Loosen the screws on pins 1 to 4 and insert the cores according to the pin numbers.




- $\bullet$  Use the dedicated Screwdriver (XW4Z-00B)\* and tighten the screws securely so that the cores do not pull out. (0.15 to 0.2 N·m)
- Five-pole Connectors
- Strip the cable sheath for a total of 15 mm and strip the core covering for 8 mm for the core to connect to pin 5.



- Connect the core to pin 5 (in the center) first.
- Insert the core from the side of the hold with the tab and tighten the screw securely (tightening torque: Pins 1 to 4: 0.15 to 0.2 N·m, Pin 5: 0.03 to 0.05 N·m), and then cut off the excess wire with wire cutters.




• Bend the cable as shown below, attached the enclosed insulation cap, and then strip the other cores.



• Connect the cores to pins 1 to 4.

#### **Connecting Shielded Cables to Five-pole Connectors**


- Place the insulation tub on the drain line of the shield and connect it to the terminal.
- Tighten the screw and then check visually to see if there is insulation between the cores.




\*When tightening the screws, use the dedicated XW4Z-00B Screwdriver that matches with the screw-slot dimensions.



#### (4) Inserting Pin Block




- Cover to the pin block so that the triangle p
- Mount the cover to the pin block so that the triangle mark on the pin block will coincide with the triangle mark on the cover.
- If the cover is used for a Right-angle model, the relationship between the position of the polarity key on the engaged side and cable connection direction will be determined by the direction in which the positioning key is inserted into the cover, which can be rotated by 90°.
- Fully insert the positioning key until the positioning key is hidden by the casing.



- Align the triangular marks on the pin block and cover and insert the pin block into the cover.
- Press them together firmly until the pin block does not come out of the cover. (0.39 to 0.49 N·m)

#### (5) Mounting Cap

- After mounting the cover to the pin block and the cover snaps into place, tighten the cap securely by hand (0.39 to 0.49 N·m)
- Note: If the cap is not tighten securely enough, the degree of protection (IP67) may not be maintained or vibration may cause the cap to become loose. Do not tighten the cap with pliers or similar tools; they may damage the cap.



• After fully tightening the cap, length A should be approximately one of the following according to the cable external diameter and the Connector model. (Use these as a guide.)

External diameter of	Cable external diameter (mm)					
applicable cable	6 mm	5 mm	4 mm	3 mm		
For 6-mm-dia. cable	1	0	—	_		
For 4-mm-dia. cable	_	2	1			
For 3-mm-dia. cable	_	_	2	1		

### (6) After Assembly


 Confirm the insulation between cores after completing assembly.

#### **Recommended Cables**

When connecting a commercially available cable to a connector assembly, use a cable with an outside diameter of 3 to 6 mm and core conductor sizes of 0.18 to 0.75 mm<sup>2</sup> for crimping connectors and 0.5 mm<sup>2</sup> maximum for soldering connectors.

### **Connector Arrangement**

For safety, when constructing a connection system between a Sensor and panel with a connector, make sure that the connector plug is on the Sensor side and the connector socket is on the panel side (i.e., the female pins are located on the power-supply side).



(Unit: mm)


## XS2P Panel-mounting Sockets for Terminal Boxes

## **Ordering Information**


No. of	Lock method	Din ohene*	Applicable wire	DC	AC	UL
poles	Lock method	Pin shape*	diameter	Model	Model	UL
	Rear lock	Solder cup pin		XS2P-D421-2	XS2P-A421-2	
4	Front lock	Solder cup pin	AWG20 to 28	XS2P-D422-2	XS2P-A422-2	– UL 2238 certified – (File No. E207683)
		DIP pin		XS2P-D422-1	XS2P-A422-1	
5	<b>_</b>	Solder cup pin		XS2P-D522-2		
	Front lock	DIP pin		XS2P-D522-1	_	

\*The solder cup pin is for wire mounting, and the DIP pin is for PCB mounting. Soldering is required for both pins.

## Dimensions




Front Lock Model XS2P-0422-1 (with DIP Pins)




Front Lock Model XS2P-D522-1 (with DIP Pins) XS2P-D522-2 (with Solder Cup Pins)











Note: The panel thickness is 1 to 4 mm.

With DIP Pins






## **Ordering Information**

Cable	Connector	D	UL	
Cable	Connector	Cable length L (m)	Model	
		0.5	XS2R-D426-B11-F	
	Connectors on	1	XS2R-D426-C11-F	
With cable	both cable ends	2	XS2R-D426-D11-F	UL 2238 certified
with cable		3	XS2R-D426-E11-F	(File No. E207683)
	Connector on one	2	XS2R-D426-D10-F	· · · · · ·
	cable end	5	XS2R-D426-G10-F	
Cable	Connector	D	C	UL
Cable	Connector	Cable length L (m)	Model	UL
			XS2R-D426-1	
Without ophio	Connectors on		XS2R-D426-1 XS2R-D426-5	UL 2238 certified
Without cable	Connectors on both cable ends			UL 2238 certified (File No. E207683)


Note: XS2G Screw-on Plugs cannot be connected side-by-side to the CN1 and CN2 connectors. Consider using a crimping or soldering model instead. Refer to page 17 for details.

## **Dimensions**


#### Connectors on Both Cable Ends (Y-Joint Plug/Socket) XS2R-D426-011-F





#### Connectors on One Cable End (Y-Joint Socket) XS2R-D426-010-F



### Y-Joint Plug/Socket without Cable XS2R-D426-1









Wiring Diagram










CN0



Vhit

(Unit: mm)

1

## XS2R T-Joint Plug/Socket Connectors


## **Ordering Information**


Туре	DC Model	UL
Aggregate model	XS2R-D422-1 XS2R-D422-5	UL 2238 certified
Bifurcated model	XS2R-D423-1	(File No. E207683)\
Daisy-chain model	XS2R-D424-1	2207000)


## Dimensions

Aggregate model XS2R-D422-1 XS2R-D422-5


















1




1 2 3 4 C (Male)

#### Daisy-chain model XS2R-D424-1










## **Features**

## **XS2R Application Examples**



## **Safety Precautions**

### Precautions for Correct Use

Do not use the product in atmospheres or environments that exceed product ratings.

• Before using the XS2R for Sensors, make sure that the wiring of the Sensors and the internal connections of the XS2R are correct.

## XS2M Sensor-embedded Plugs


## **Ordering Information**

No. of poles	Mounting method	Pin shape	Applicable wire di- ameter	DC Model	AC Model	UL
4	Embedded with screw threads	O a la la mana a la	AWG22 to 28	XS2M-D421	XS2M-A421	UL 2238 certified (File No. E207683)
4	Embedded without screw threads	Solder cup pin		XS2M-D422	XS2M-A422	

## Dimensions




Resin filled



Embedded without screw threads

XS2M-D422 (For DC) XS2M-A422 (For AC)



9.6 dia. O-ring

-10.8-11.2

16

9.4 dia

0.7

5 dia.

10.5 dia

45°-


AC

45°-⊫ 5 dia

DC

**Mounting Dimensions** 

9.45+0.0



Note: After mounting, anchor the solder cup pins by injecting resin.

OMRON

## XS2M Panel-mounting Plugs

## **Ordering Information**

No. of poles	Mounting method	Pin shape*1	Applicable wire diameter	DC Model	AC Model	UL
	Flange-mounting	Solder cup pin	AWG22 to 28	XS2M-D423	XS2M-A423	
4	Screw-mounting	DIP pin	—	XS2M-D424-1	XS2M-A424-1	
	Screw-mounting	Solder cup pin		XS2M-D424-2	XS2M-A424-2	UL 2238 certified (File No. E207683)
-	Correct measurations	Solder cup pin	AWG20 to 28	XS2M-D524-2	_	(The NO. L207003)
5	Screw-mounting	Solder cup pin		XS2M-D524-4 *2	-	
1. The solde	r cup pin is for wire mounting,	and the DIP pin is for PC	B mounting. Not	e: 4-pole DC screw-mou	nting models (XS2M-D42	$24-\Box$ ) with metal bodies are

Soldering is required for both pins.

\*2. XS2M-D524-4 plugs have a metal body.

also available.

Ask your OMRON representative for details.


## Dimensions

(Unit: mm)


16<sup>+0.3</sup> dia.


Land

Panel Cutout



#### Screw-mounting XS2M-Q424-1 For DIP (Resin Body) XS2M-0424-2 Solder Cup Pins (Resin Body)






## **Common Accessories and Tools (Order Separately)**

## **Ordering Information**

## **Connector Covers**



#### **Application Example: XS2Z-11**




You can use the Waterproof Cover when the connector is not connected to ensure an IP67 degree of protection. When mounting the Water-resistive Cover to a Connector, be sure to apply a torque range between 0.39 and 0.49 N·m to tighten the Water-resistive Cover.

Model	Materials	Suitable connector			
wouer	Wateriais	Model	Mounting portion		
XS2Z-11	Due es /sieles la lata d	XS2G/XS2H/XS2M/XS2R/XS2W/XS5H/ XS5M/XS5W	M12 male screw		
XS2Z-22	Brass/nickel plated	XS2C/XS2R/XS2F/XS2P/XS2W/XW3B/ XS5F/XS5W/XS5R/XS5P/XW3D	M12 female screw (thread bracket)		


#### **Dust Covers**

XS2Z-13





M12 female screw (thread bracket)




#### **Application Example: XS2Z-13**



The Dust Cover is for dust prevention and does not ensure IP67 degree of protection. When mounting the Dust Cover to a Connector, be sure to press the Dust Cover onto the Connector until

the Connector is fully inserted into the Dust Cover.

		Pin block (temale pins)			
Model	Materials	Suitable connector			
Model		Model	Mounting portion		
XS2Z-13	Rubber/black	XS2G/XS2H/XS2M/XS2R	M12 male screw		
XS2Z-14		XS2C/XS2R/XS2F/XS2P/XW3B	Pin block (female pins)		
XS2Z-15		1320/1320/132F/152F/152F/2W3B	M12 female screw (thread bracket)		




#### XY2F-0001

Use this tool to extract a Pin Block from the covers in order to make wiring changes or corrections after the cover has been mounted to the pin block for Connector Assemblies (XS2C/XS2G, soldering/crimping).




## **Extraction Procedure**

(1) Disconnecting ComponentsDisconnect all components on the cap side from the cover.




(2) Extracting Pin Block


• Insert the claws of the Tool into the four holes of the cover.



• Make sure that the pin block is outside the Tool.



• Press the Tool so that the guides of the Tool are in close contact. Then pull the pin block straight.



#### Precautions for Correct Use

- The pin block must not be extracted from the same Connector more than 3 times, otherwise the proper degree of protection of the pin block or Connector will not be maintained.
- Do not use the product in atmospheres or environments that exceed product ratings.

#### **Tightening Cap (Connector Assemblies)**


 Do not use pliers to tighten caps, otherwise the caps may be damaged. Use your fingers to tighten the Connectors sufficiently.

(0.39 to 0.49 N·m)

2) If caps are not tightened securely, the Connectors may not maintain their proper degree of protection (i.e., IP67) or the caps may become loose due to vibration.

#### **Connector Connection and Disconnection**

- When connecting or disconnecting Connectors, be sure to hold the Connectors by hand.
- Do not hold the cable when disconnecting Connectors.
- Connectors mating with sockets must be fully inserted into the mating sections. Tighten the thread bracket carefully so that the threads will not be damaged.
- Fully tighten thread bracket within a torque range between 0.39 and 0.49 N·m and be sure that the threads of the opposite parts are hidden by the thread bracket.
- When disconnecting Connectors, be sure to loosen the thread brackets first. Do not loosen the caps.
- Thread brackets must be loosened in the cutout direction.



#### **Degree of Protection**

- Do not impose external force continuously on the joints of pin blocks and covers, otherwise the Connectors may not keep its proper degree of protection (i.e., IP67).
- The degree of protection of connectors (IP67) is not for a fully watertight structure. Do not use them underwater.
- Connectors are of resin mold construction. Do not impose excessive force on them.

#### Setup

- Do not make any cable bends near the base of the Unit.
- Any bends made must have a minimum radius of 40 mm.

### Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warrantv.

See http://www.omron.com/global/ or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2020.11

In the interest of product improvement, specifications are subject to change without notice.

**OMRON** Corporation Industrial Automation Company

http://www.ia.omron.com/